

| | | | | |
|--------------------------------------|-----------------------|-----|-----------------|--|
| Product designation | | | | Signal beacons |
| Product type designation | | | | Ø62mm/2.44" 8LB6S |
| General characteristics | | | | |
| Diameter | | | mm - inch | 62mm / 2.44" |
| Supply voltage (AC) | | | V | 24 |
| Supply voltage (DC) | | | V | 24 |
| Colour | | | | Yellow |
| Material | | | | Polycarbonate |
| IEC degree of protection | | | | IP54 |
| Sound module consumption (AC) | | | mA | 150 |
| Sound module consumption (DC) | | | mA | 150 |
| Sound intensity | | | dB | 80dB/1m |
| Mechanical features | | | | |
| Tightening torque for terminals max | | | Nm | 0.5 |
| Terminals screw | | | | Screw clamp terminals |
| Conductor section | AWG/Kcmil | | | |
| | | max | | 16 |
| | IEC | | | |
| | | max | mm ² | 1.5 |
| Weight | | | g | 60 |
| Ambient conditions | | | | |
| Temperature | Operating temperature | | | |
| | | min | °C | -20 |
| | | max | °C | +50 |
| Dimensions | | | | |
| Wiring diagrams | | | | |
| Certifications and compliance | | | | |
| Compliance | IEC/EN 60947-1 | | | |
| | IEC/EN 60947-5-1 | | | |
| Certificates | EAC | | | |
| ETIM classification | | | | |
| ETIM 8.0 | | | | EC000232 - Optical module for signal tower |