

Single Row Terminal Blocks

Kulka® 699/899 Series

150 Volts



Specifications:

- Base, Phenolic, 150° C
- Open Back Design (Insulator Strip Required for Voltage Rating)
- JJ (GDI-30F) Material Available
- Screws, #6-32 Binder Head, Phil-Slot
- Terminals, Plated Brass
- 1-23 Poles
- 7/16" Centers
- Wire Range With Wire Binding Screw #14-#16 AWG – 20 Amps
- The Suitability Of These Devices For Greater Currents Shall Be Determined In The End-Use Application
- UL Recognized File No. E47811
- CSA Certified File No. LR19766
- 899 Series (Riveted KT's)
- C€

Hardware Options: (Hardware options may affect ratings - consult factory)

Catalog Description	Number of Poles	Dimensions	
		A	B
699 GP 01	1	1.19	0.88
699 GP 02	2	1.63	1.31
699 GP 03	3	2.06	1.75
699 GP 04	4	2.50	2.19
699 GP 05	5	2.94	2.63
699 GP 06	6	3.38	3.06
699 GP 07	7	3.81	3.50
699 GP 08	8	4.25	3.94
699 GP 09	9	4.69	4.38
699 GP 10	10	5.12	4.81
699 GP 11	11	5.56	5.25
699 GP 12	12	6.00	5.69
699 GP 13	13	6.44	6.13
699 GP 14	14	6.87	6.56
699 GP 15	15	7.31	7.00
699 GP 16	16	7.75	7.44
699 GP 17	17	8.19	7.88
699 GP 18	18	8.62	8.31
699 GP 19	19	9.06	8.75
699 GP 20	20	9.50	9.19
699 GP 21	21	9.94	9.63
699 GP 22	22	10.37	10.06
699 GP 23	23	10.81	10.50

MM=Dim X 25.4

KT 46	=	Full Quick Connect (0° Flat)	See Page 92
KT 47	=	Full Quick Connect (45° Bend)	See Page 92
KT 48	=	Full Quick Connect (90° Bend)	See Page 92
J 601	=	Line to Line Jumper	See Page 96
601 RJ(S)	=	Multiple Position Jumper	See Page 96
3/4 ST	=	Half Solder	See Page 94
KT 52	=	Half Quick Connect (0° Flat)	See Page 92
KT 53	=	Half Quick Connect (45° Bend)	See Page 92
KT 54	=	Half Quick Connect (90° Bend)	See Page 92
Z	=	Lug Over the Side (.437)	See Page 95
2102	=	Stud	See Page 98
2104	=	Feed Thru Solder	See Page 98
2120	=	Solder Pin	See Page 98
2121	=	Solder Pin	See Page 98

