

|                                      |                             |                 |            |   |
|--------------------------------------|-----------------------------|-----------------|------------|---|
| Product designation                  |                             |                 |            | LED elements  |
| Product type designation             |                             |                 |            | steady light  |
| <b>General characteristics</b>       |                             |                 |            |   |
| Colour                               |                             |                 |            | Red   |
| <b>Electrical characteristics</b>    |                             |                 |            |   |
| Rated frequency                      | Hz                          |                 |            | 50/60   |
| Supply voltage (AC)                  | V                           |                 |            | 185...265   |
| <b>Operations</b>                    |                             |                 |            |   |
| Electrical life                      | hours                       |                 |            | 100000  |
| <b>Mechanical features</b>           |                             |                 |            |   |
| Tightening torque for terminals max  | Nm                          |                 |            | 1   |
| Conductor section                    | AWG/kcmil conductor section |                 |            |   |
|                                      |                             | max             | 12         |   |
|                                      | IEC                         |                 |            |   |
|                                      | max                         | mm <sup>2</sup> | 1 or 2 2.5 |   |
| Mounting adapter                     |                             |                 |            | LM2TAU120   |
| Weight                               | g                           |                 |            | 16  |
| <b>Ambient conditions</b>            |                             |                 |            |   |
| Temperature                          | Operating temperature       |                 |            |   |
|                                      | min                         | °C              | -25        |   |
|                                      | max                         | °C              | +60        |   |
|                                      | Storage temperature         |                 |            |   |
|                                      | min                         | °C              | -40        |   |
|                                      | max                         | °C              | +85        |   |
| <b>Dimensions</b>                    |                             |                 |            |   |
| <b>Wiring diagrams</b>               |                             |                 |            |   |
| <b>Certifications and compliance</b> |                             |                 |            |   |
| Compliance                           | CSA C22.2 n° 14             |                 |            |   |
|                                      | IEC/EN 60947-1              |                 |            |   |
|                                      | IEC/EN 60947-5-1            |                 |            |   |
|                                      | UL508                       |                 |            |   |
| Certificates                         | CCC                         |                 |            |   |
|                                      | cULus                       |                 |            |   |
|                                      | EAC                         |                 |            |   |
| <b>ETIM classification</b>           |                             |                 |            |   |
| ETIM 8.0                             |                             |                 |            | EC000204 -<br>Lamp holder<br>block for control<br>circuit devices |