


LTR	REVISION	DATE	APPD
D	030923-UF01: ADDED TEST DATA @24VDC FOR BPF120-XIW-028V	03-10-23	HF

**NOTES:**

1. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
2. SLEEVE MATERIAL: EPOXY

REVISION NOTIFICATION

- ☐ DLC
- ☐ UL/ETL
- ☐ MADE IN USA
- ☐ CUSTOMER _____
- ☐ OTHER _____

REDLINE CHECKLIST

- ☐ REDLINE(YES)
- ☐ DATE: _____
- ☐ INITIATED BY: _____
- ☐ ECR REQUIRED YES ☐ NO ☐
- ☐ WORK ORDER# _____

ELECTRO-OPTICAL CHARACTERISTICS (Ta = 25°C)

BPF120-0AG-028V	AQUA GREEN	28Vdc	0.4 W	0.015 A	4.1 lm	0.33	0.20 cd	521	120°
BPF120-0CW-028V	COOL WHITE	28Vdc	0.4 W	0.015 A	5.9 lm	0.47	0.10 cd	8000K	120°
BPF120-0UR-028V	ULTRA RED	28Vdc	0.6 W	0.020 A	0.3 lm	0.03	0.03 cd	651	120°
BPF120-0UY-028V	SUPER YELLOW	28Vdc	0.6 W	0.020 A	0.9 lm	0.08	0.02 cd	590	120°
BPF120-XIW-028V	WARM WHITE	24Vdc	0.2 W	0.010 A	4.0 lm	0.32	1.61 cd	3000K	105°
		28Vdc	0.3 W	0.012 A	4.6 lm	0.37	1.98 cd		
LEDTRONICS PART NO.	COLOR EMITTED	INPUT VOLTAGE, V typ.	POWER (W)	CURRENT (A)	LUMENS	SCP	LUMINOUS INTENSITY	λ_P nm COLOR TEMP. (K)	VIEWING ANGLE (FULL BEAM WIDTH @ 50% INTENSITY)

LED[®]
LEDTRONICS, TM INC.
23105 KASHIWA COURT
TORRANCE, CA 90505

-PROPRIETARY-
This document contains Proprietary
information of LEDTRONICS, INC.
It may not be copied, used or disclosed
for any purpose without the prior express
written consent of LEDTRONICS, INC.

.XXX ± .010 TOLERANCE PER ANSI-Y14.5
.XX ± .025 (UNLESS OTHERWISE STATED)
ANGLES ± 0°, 30'
FRACT. ± 1/32

TITLE BPF120-XXX-028V							
DWG NO		SCALE		SHEET		DATE	
BPF120-28V-DC		2:1		1 OF 1		07-29-10	
CODE IDENT NO.	DWG BY GP	CHK BY	QA LUV	MFG LUV	R&D UF		
8Z410	07-29-10		03-21-23	03-21-23	03-21-23		