


LTR	REVISION	DATE	APPD
-	RELEASED	08-20-09	



HOLDER MATERIALS AND FINISHES:

HOUSING: ALUMINUM WITH BLACK ANODIZED FINISH
 HEX NUT: STEEL. ZINC PLATED WITH YELLOW IRIDESCENT CHROMATE FINISH
 INTERNAL-TOOTH LOCKWASHER: STEEL. ZINC PLATED WITH YELLOW IRIDESCENT CHROMATE FINISH
 TERMINALS: BRASS, TIN PLATED WITH ELONGATED SLOT

NOTES:

1. MOUNTING DIAMETER 15/32"
2. HOLDER ACCEPTS T1-3/4 MIDGET FLANGE BASE LED LAMP.
3. HOLDERS MEET MIL SPEC MIL-3661
4. MFS470B IS MIL TYPE LH73/1
5. ALL PARTS WITH (*) ARE "RoHS" CERTIFIED.

MFS470-0AG-028B*	MFS470CAG6K-28V-BP	AQUA GREEN	28	12-15	500	518	120°	*
MFS470-0CW-028B*	-	COOL WHITE	28	12-15	300	8000K	120°	*
MFS470-0UG-028B*	-	SUPER GREEN	28	12-15	50	570	120°	*
MFS470-0UO-028B	MFS470C03K-28V-BP	SUPER ORANGE	28	18-20	-	612	75°	
MFS470-0UR-028B*	-	ULTRA RED	28	18-20	-	652	65°	*
MFS470-0UY-028B	-	SUPER YELLOW	28	18-20	-	599	105°	
LEDTRONICS PART NO.	PART NO. DESCRIPTION	COLOR EMITTED	SET VOLTS	READ mA typ	lv mod typ	λP nm	VIEWING ANGLE	
ELECTRICAL TEST								



 23105 KASHIWA COURT TORRANCE, CA 90505	-PROPRIETARY- This document contains Proprietary information of LEDTRONICS, INC. It may not be copied, used or disclosed for any purpose without the prior express written consent of LEDTRONICS, INC.		TITLE MFS470-0XX-028B			
	.XXX ± .010 TOLERANCE PER ANSI-Y14.5 .XX ± .025 (UNLESS OTHERWISE STATED) ANGLES ± 0°,30' FRACT. ± 1/32		DWG NO MFS470-28V-BP	SCALE 1:1	SHEET 1 OF 1	DATE 08-20-09
	CODE IDENT NO. 8Z410	DWG BY GP 08-20-09	CHK BY PL 08-25-09	QA CH 08-24-09	MFG LD 08-24-09	R&D