


LTR	REVISION	DATE	APPD
-	RELEASED	01-03-20	



NOTES:

1. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
2. SLEEVE MATERIAL / COLOR: NYLON 66 (UL94V-1 MINIMUM, UL94V-0 PREFERRED) / BLACK
3. MOUNTING DIAMETER: Ø5/16"

REVISION NOTIFICATION	
<input type="checkbox"/> DLC	
<input type="checkbox"/> UL/ETL	
<input type="checkbox"/> MADE IN USA	
<input type="checkbox"/> CUSTOMER _____	
<input type="checkbox"/> OTHER _____	
REDLINE CHECKLIST	
<input type="checkbox"/> REDLINE(YES)	
<input type="checkbox"/> DATE: _____	
<input type="checkbox"/> INITIATED BY: _____	
<input type="checkbox"/> ECR REQUIRED YES <input type="checkbox"/> NO <input type="checkbox"/>	
<input type="checkbox"/> WORK ORDER# _____	

ELECTRICAL-OPTICAL CHARACTERISTICS (Ta = 25°C)

PPD312-OUR-028V-W6	ULTRA RED	24/28Vdc	0.017 A	0.48 W	0.900 cd	WATERCLEAR	652	15°
PPD312-1AG-028V-W6	SUPER AQUA GREEN	24/28Vdc	0.013 A	0.36 W	1.500 cd	WATERCLEAR	521	16°
LEDTRONICS PART NO.	COLOR EMITTED	INPUT VOLTAGE, V (Tested@28Vdc)	CURRENT (A)	POWER (W)	MAXIMUM CANDELA	LENS TYPE/COLOR	λP nm	VIEWING ANGLE (FULL BEAM WIDTH @ 50% INTENSITY)

<p>LEDTRONICS,™ INC. 23105 KASHIWA COURT TORRANCE, CA 90505</p>	<p>-PROPRIETARY- This document contains Proprietary Information of LEDTRONICS, INC. It may not be copied, used or disclosed for any purpose without the prior express written consent of LEDTRONICS, INC.</p>		<p>TITLE PPD312-XXX-028V-W6</p>						
	<p>.XXX ± .010 TOLERANCE PER ANSI-Y14.5 .XX ± .025 (UNLESS OTHERWISE STATED) ANGLES ± 0°,30' FRACT. ± 1/32</p>		<p>DWG NO PPD312-28V-W6</p>	<p>SCALE 1:1</p>	<p>SHEET 1 OF 1</p>	<p>DATE 01-03-20</p>			
	<p>CODE IDENT NO. 8Z410</p>	<p>DWG BY HF 01-03-20</p>	<p>CHK BY</p>	<p>QA SB 01-10-20</p>	<p>MFG LD 01-10-20</p>	<p>R&D UF 01-10-20</p>			