

4570-CA



UPC Code : 078477795699

Country Of Origin : United States

RoHS Compliant : Yes



Locking Plug, 15 Amp, 250 Volt, Industrial Grade, Black & White

15 Amp, 250 Volt, NEMA L6-15P, 2P, 3W, Locking Plug, Industrial Grade, Grounding, Angle - BLACK-WHITE

Leviton's Black & White line of industrial grade plugs, connectors, flanged inlets, and outlets offer superior performance, long lasting reliability and features that are backed by a limited lifetime warranty:

One piece contacts reduce friction and overheating

Unique cord clamp accepts wide range of cord sizes

Rugged nylon construction resists impact, sunlight, chemicals, and rough use

Industry exclusive limited lifetime warranty

Made proudly in the USA

Technical Information

Mechanical Specifications

Cord Range : .240 - .700

Horsepower Rating : 1-1/2 HP

Product ID : Ratings and NEMA I.D. permanently marked on device

Terminal Accom. : 18-10 AWG

Terminal ID : Brass-Hot, Green-Ground, Silver-Neutral

Torque Range : 10-14 in-lbs

Wire Gauge : 18-10 AWG

Electrical Specifications

Amperage : 15 A

Current Interrupting : Certified for current interrupting at full rated current

Dielectric Voltage : Withstands 2000V per UL498

Grounding : Grounding

Pole : 2

Temperature Rise : Max 30C after 250 cycles OL at 200 percent rated current

Voltage : 250 VAC

Wire : 3

Environmental Specifications

Environment : Dry

Flammability : Rated HB or better UL94

Operating Temperature : -40°C to 60°C

Material Specifications

Assembly Screws : Steel, Zinc Plated

Back Cover : Thermoplastic

Blades/Contacts : Solid Brass

Body Material : Impact Modified Nylon

Clamp Insert : Nylon

Color : Black-White

Cord-Clamp : Nylon

Terminal Screws : Brass

Wire Module : Nylon

Product Features

Brand : Black and White

Color : Black-White

Feature : Angled

NEMA : L6-15P

Standards and Certifications

ANSI : C-73

CSA C22.2 No. 42 : File LR-406


NEMA : WD-6

NOM Certified : 057

UL Fed Spec WC-596 : File E13393

Warranty : Limited Lifetime Warranty

Dimensional Diagram



SPECIFICATION SUBMITTAL

JOB NAME:		CATALOG NUMBERS:	
<input type="text"/>		<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):

+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2021 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

