

# 303 Series

## TR3, Fast-Acting Fuse



### Description

The 303 Series are TR3, fast-acting type, 125V rated fuses designed in accordance to UL 248-14.

### Features & Benefits

- Reduced PCB space requirements
- Direct solderable or plug-in versions
- Internationally approved
- Low internal resistance
- Shock safe casing
- Vibration resistant
- RoHS compliant, Lead-Free and Halogen-Free
- Available from 0.050A to 5A

### Additional Information



Resources



Accessories



Samples

### Electrical Characteristics

| % of Ampere Rating | Opening Time        |
|--------------------|---------------------|
| 200                | 60 Seconds, Maximum |

### Applications

- Battery chargers
- Consumer electronics
- Power supplies
- Industrial controllers

### Agency Approvals

| Agency | Agency File Number | Ampere Range |
|--------|--------------------|--------------|
| UL     | E67006             | 0.050A - 5A  |
| CSA    | 051378             | 0.050A - 5A  |
| UKCA   | NA                 | 0.050A - 5A  |

### Electrical Characteristics


| Amp Code | Rated Current | Voltage Rating | Breaking Capacity           | Nominal Cold Resistance (Ohms) | Voltage Drop 1.0xI <sub>N</sub> max. (mV) | Power Dissipation 1.0xI <sub>N</sub> max. (mW) | Melting Integral 10xI <sub>N</sub> max. (A <sup>2</sup> s) | Approvals |      |     |
|----------|---------------|----------------|-----------------------------|--------------------------------|-------------------------------------------|------------------------------------------------|------------------------------------------------------------|-----------|------|-----|
|          |               |                |                             |                                |                                           |                                                |                                                            | UL        | UKCA | CSA |
| 0050     | 50mA          | 125V           | 50A @ 125VAC<br>50A @ 63VDC | 2.9203                         | 800                                       | 40                                             | 0.00007                                                    | X         | X    | X   |
| 0063     | 63mA          | 125V           |                             | 2.7400                         | 780                                       | 50                                             | 0.00013                                                    | X         | X    | X   |
| 0080     | 80mA          | 125V           |                             | 2.2300                         | 730                                       | 60                                             | 0.0002                                                     | X         | X    | X   |
| 0100     | 100mA         | 125V           |                             | 4.3800                         | 700                                       | 70                                             | 0.0004                                                     | X         | X    | X   |
| 0125     | 125mA         | 125V           |                             | 3.4605                         | 650                                       | 85                                             | 0.0022                                                     | X         | X    | X   |
| 0160     | 160mA         | 125V           |                             | 2.1687                         | 600                                       | 100                                            | 0.0029                                                     | X         | X    | X   |
| 0200     | 200mA         | 125V           |                             | 1.3500                         | 550                                       | 110                                            | 0.0042                                                     | X         | X    | X   |
| 0250     | 250mA         | 125V           |                             | 1.1500                         | 500                                       | 125                                            | 0.0082                                                     | X         | X    | X   |
| 0315     | 315mA         | 125V           |                             | 0.9645                         | 450                                       | 145                                            | 0.015                                                      | X         | X    | X   |
| 0400     | 400mA         | 125V           |                             | 0.8050                         | 400                                       | 160                                            | 0.025                                                      | X         | X    | X   |
| 0500     | 500mA         | 125V           |                             | 0.5320                         | 380                                       | 190                                            | 0.042                                                      | X         | X    | X   |
| 0630     | 630mA         | 125V           |                             | 0.1448                         | 160                                       | 100                                            | 0.015                                                      | X         | X    | X   |
| 0800     | 800mA         | 125V           |                             | 0.1023                         | 155                                       | 125                                            | 0.025                                                      | X         | X    | X   |
| 1100     | 1.00A         | 125V           |                             | 0.0830                         | 150                                       | 155                                            | 0.039                                                      | X         | X    | X   |
| 1125     | 1.25A         | 125V           |                             | 0.0644                         | 145                                       | 185                                            | 0.059                                                      | X         | X    | X   |
| 1160     | 1.60A         | 125V           |                             | 0.0520                         | 140                                       | 225                                            | 0.11                                                       | X         | X    | X   |
| 1200     | 2.00A         | 125V           |                             | 0.0400                         | 130                                       | 260                                            | 0.17                                                       | X         | X    | X   |
| 1250     | 2.50A         | 125V           |                             | 0.0307                         | 125                                       | 315                                            | 0.23                                                       | X         | X    | X   |
| 1315     | 3.15A         | 125V           |                             | 0.0262                         | 120                                       | 380                                            | 0.45                                                       | X         | X    | X   |
| 1400     | 4.00A         | 125V           |                             | 0.0178                         | 110                                       | 440                                            | 1.0                                                        | X         | X    | X   |
| 1500     | 5.00A         | 125V           |                             | 0.0131                         | 105                                       | 525                                            | 1.5                                                        | X         | X    | X   |

Note: 1.00 means the number one with two decimal places. 1,000 means the number one thousand.

# 303 Series


## TR3, Fast-Acting Fuse

### Temperature Re-rating Curve




**Note:** Re-rating depicted in this curve is in addition to the standard derating of 25% for continuous operation.

### Average Time Current Curves



### Soldering Parameters - Wave Soldering



### Recommended Process Parameters:

| Wave Parameter                                       | Lead-Free Recommendation          |
|------------------------------------------------------|-----------------------------------|
| Preheat:<br>(Depends on Flux Activation Temperature) | (Typical Industry Recommendation) |
| Temperature Minimum:                                 | 100°C                             |
| Temperature Maximum:                                 | 150°C                             |
| Preheat Time:                                        | 60-180 seconds                    |
| Solder Pot Temperature:                              | 260°C Maximum                     |
| Solder Dwell Time:                                   | 2-5 seconds                       |

### Recommended Hand-Solder Parameters:

Solder Iron Temperature: 350°C +/- 5°C  
Heating Time: 5 seconds max.

**Note:** These devices are not recommended for IR or Convection Reflow process.

# 303 Series


## TR3, Fast-Acting Fuse

### Product Characteristics


|                                  |                                                                                                                                      |
|----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|
| <b>Materials</b>                 | Base/Cap: Black Thermoplastic Base<br>Polyamide PA 6.6, UL 94V-0<br>Brass, Nickel-plated Cap<br>Round Pins: Copper alloy, Tin-plated |
| <b>Lead Pull Strength</b>        | 10 N (IEC 60068-2-21)                                                                                                                |
| <b>Solderability</b>             | 260°C, ≤ 3s. (Wave)<br>350°C, ≤ 1s. (Soldering Iron)                                                                                 |
| <b>Soldering Heat Resistance</b> | 260°C, 10s. (IEC 60068-2-20)<br>350°C, 3s. (Soldering Iron)                                                                          |

|                              |                                                                                                      |
|------------------------------|------------------------------------------------------------------------------------------------------|
| <b>Operating Temperature</b> | -25°C to +70°C (consider de-rating)                                                                  |
| <b>Climatic Category</b>     | -25°C/+70°C/21 days<br>(IEC 60068-1-3)                                                               |
| <b>Stock Conditions</b>      | +10°C to +60°C RH,<br>≤75% yearly average, without dew<br>24 cycles at 15 min. each<br>(IEC 60068-6) |
| <b>Vibration Resistance</b>  | 10 - 60 Hz at 0.75 mm amplitude<br>60 - 2000 Hz at 10 g acceleration                                 |

### Dimensions



### Part Numbering System



### Packaging

| Packaging Option  | Packaging Specification | Quantity | Quantity & Packaging Code | Reel Size |
|-------------------|-------------------------|----------|---------------------------|-----------|
| <b>303 Series</b> |                         |          |                           |           |
| Tape & Ammopack   | N/A                     | 1,500    | 0001                      | N/A       |
| Long Leads        | N/A                     | 200      | 0131                      | N/A       |
| Short Leads       | N/A                     | 300      | 0421                      | N/A       |

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics)