

ANT-W63-FPC-LV100UF

✓ ACTIVE

TE Internal #: L9000211-01
Flexible PCB (FPC) Antenna, Triple Band, Wi-Fi, Internal
/Embedded Mount, Adhesive Mount, N-type, Omnidirectional,
Single Port, > 6 dBi Peak Gain
[View on TE.com >](#)



Antennas



Communication Protocol: **Wi-Fi**
Mounting Location: **Internal/Embedded**
Mounting Type: **Adhesive Mount**
Frequency Category: **2400 – 7125**
Antenna Type: **Flexible PCB (FPC)**

Features

Product Type Features

Antenna Termination	N-type
Antenna Product Type	Antenna

Configuration Features

Mounting Location	Internal/Embedded
Antenna Type	Flexible PCB (FPC)
Band Type	Triple Band
Port Configuration	Single Port

Signal Characteristics

Frequency Category	2400 – 7125
Peak Gain	> 6 dBi

Mechanical Attachment

Mounting Type	Adhesive Mount
---------------	----------------

Operation/Application

Directionality	Omnidirectional
----------------	-----------------

Industry Standards

Communication Protocol	Wi-Fi
Primary Application	Wi-Fi



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CONUFL001-SMD
Conn UFL MHF Straight PCB Mount Jack



TE Part # CONMHF1-SMD-T
U.FL/MHF1 Jack 50 Ohm PCB Surface Mount



TE Part # CONMHF1-SMD-G-T
U.FL/MHF1 Jack 50 Ohm PCB Surface Mount



TE Part # CONUFL001-SMD-T
U.FL/MHF1 Jack 50 Ohm PCB Surface Mount

Customers Also Bought

ANT-W63-FPC-LV100UF

Flexible PCB (FPC) Antenna, Triple Band, Wi-Fi, Internal/Embedded Mount, Adhesive Mount, N-type, Omnidirectional, Single Port, > 6 dBi Peak Gain





TE Part #GA10K3A1IB
DISCRETE 10K OHMS,+/-0.2C FROM
0C TO 70C



TE Part #L9000230-01
Antenna WiFi6/6E FPC 20x110 100 UFL



TE Part #1-34070-1
PG BUTT SPLC 22-16COMM22-18MIL



TE Part #2-34854-1
TERMINAL,PG R 12-10 10



TE Part #440129-8
2.0MM,HSG,8POS



TE Part #4-794677-2
12POS MICRO MNL ASSY,R/A,THRU



TE Part #3-794680-4
04P MICRO MNL ASSY,VRT,THRU LF



TE Part #3-794680-6
06P MICRO MNL ASSY,VRT,THRU LF



TE Part #2-1445051-2
MICRO MNL HDR ASSY S/ROW LF



TE Part #2342839-2
AVP19M FLAT AIB RGB R 500MM/1X6

Documents

Product Drawings

Antenna WiFi6/6E FPC LV 7x45 100 UFL

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_L9000211-01_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_L9000211-01_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_L9000211-01_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Flexible Embedded WiFi 6/6E FPC Antennas

English

ANT-W63-FPC-LV100UF

Flexible PCB (FPC) Antenna, Triple Band, Wi-Fi, Internal/Embedded Mount, Adhesive Mount, N-type, Omnidirectional, Single Port, > 6 dBi Peak Gain

