



Product designation				Enclosed switch disconnecter
Product type designation				GAZ
Number of poles		Nr.	4	
Operating voltage type				AC
<b>Contact characteristics</b>				
IEC Conventional free air thermal current I <sub>th</sub>		A	125	
Rated insulation voltage U <sub>i</sub> IEC/EN		V	1000	
Rated impulse withstand voltage U <sub>imp</sub>		kV	8	
Operating current I <sub>e</sub>				
AC21A				
	400V	A	125	
	500V	A	125	
	690V	A	125	
AC22A				
	400V	A	125	
	500V	A	125	
	690V	A	125	
AC23A				
	400V	A	125	
	500V	A	100	
	690V	A	47	
Power dissipation per pole max		W	6.3	
Rated operational power AC23A				
	400V	kW	55	
	690V	kW	45	
Conditional short-circuit current (rms)		kA	50	
Short-circuit protection with fuse		Class/A	gG125	
Making capacity AC23A 400V		A	1250	
Breaking capacity AC23A 400V		A	1000	
Mechanical life		cycles	30000	
Electrical life AC21A		cycles	30000	
<b>Mechanical features</b>				
Operating position		normal allowable	Vertical plan Any	
Terminals		type	Pillar	
		width	mm	12.4
		height	mm	10.4
		screw	M8	
		tool	Metric Allen key 4	
Tightening torque for terminals				
	min	Nm	5	
	max	Nm	6	

	min	lbin	45
	max	lbin	54
<b>Conductor section</b>			
	IEC min	mm <sup>2</sup>	4
	IEC max	mm <sup>2</sup>	70
	AWG/kcmil min		12
	AWG/kcmil max		1

**UL technical data**

General purpose current rating	A	100
--------------------------------	---	-----

Operating voltage max	V	600
-----------------------	---	-----

Horsepower/FLA current single phase motor	120V	HP	7.5/80
	240V	HP	100/50

Horsepower/FLA current three phase motor	240V	HP	30/80
	480V	HP	60/77
	600V	HP	60/62

Short circuit rating	kA rms	50
----------------------	--------	----

Short circuit rating with fuse	Class/A	J/100
--------------------------------	---------	-------

**Ambient conditions**

Operating temperature	min	°C	-25
	max	°C	+55

Storage temperature	min	°C	-40
	max	°C	+70

Max altitude	m	3000
--------------	---	------

**Resistance & Protection**



Frontal IP degree	IP65
-------------------	------

UL degree of protection	UL/CSA Type 4/4X
-------------------------	------------------


IP degree of protection	IP65
-------------------------	------

Pollution degree	3
------------------	---

**Dimensions**



**Wiring diagrams**



### Certifications and compliance

#### Compliance

IEC/EN 60947-1

IEC/EN 60947-3

#### Certifications

cULus

EAC

### ETIM classification

ETIM 8.0

EC000216 -  
Switch  
disconnector