

| | | | |
|--------------------------------------|--|--------------|---------------------|
| Product designation | Signal beacons | | |
| Product type designation | Ø62mm/2.44" | | |
| | 8LB6GL | | |
| General characteristics | | | |
| Diameter | mm - inch | 62mm / 2.44" | |
| Supply voltage (AC) | V | 24...230 | |
| Colour | Blue | | |
| Material | Polycarbonate | | |
| IEC degree of protection | IP54 | | |
| Mechanical features | | | |
| Tightening torque for terminals max | Nm | 0.5 | |
| Terminals screw | Screw clamp terminals | | |
| Conductor section | | | |
| | AWG/Kcmil | | |
| | | max | 16 |
| | IEC | | |
| | | max | mm ² 1.5 |
| Weight | | g | 60 |
| Ambient conditions | | | |
| Temperature | Operating temperature | | |
| | | min | °C -20 |
| | | max | °C +50 |
| Dimensions | | | |
| Wiring diagrams | | | |
| Certifications and compliance | | | |
| Compliance | IEC/EN 60947-1 | | |
| | IEC/EN 60947-5-1 | | |
| Certificates | EAC | | |
| ETIM classification | | | |
| ETIM 8.0 | EC000232 - Optical module for signal tower | | |