

|                                      |   |                 |              |
|--------------------------------------|---|-----------------|--------------|
| Product designation                  | LED elements steady light base mount on LPZ control station |                 |              |
| Product type designation             | LPXLPB  |                 |              |
| <b>General characteristics</b>       |   |                 |              |
| Colour                               | Yellow  |                 |              |
| <b>Electrical characteristics</b>    |   |                 |              |
| Rated frequency                      | Hz  | 50-60           |              |
| Supply voltage (AC)                  | V   | 85...140        |              |
| <b>Operations</b>                    |   |                 |              |
| Electrical life                      | hours   | 100000          |              |
| <b>Mechanical features</b>           |   |                 |              |
| Conductor section                    | AWG/kcmil conductor section                                 |                 |              |
|                                      | max   | 14              |              |
|                                      | IEC   |                 |              |
|                                      | max   | mm <sup>2</sup> | 1 or 2 / 2.5 |
| Mounting adapter                     | LPXAU120  |                 |              |
| Weight                               | g   | 16              |              |
| <b>Ambient conditions</b>            |   |                 |              |
| Temperature                          | Operating temperature                                       |                 |              |
|                                      | min   | °C              | -25          |
|                                      | max   | °C              | +70          |
|                                      | Storage temperature   |                 |              |
|                                      | min   | °C              | -40          |
|                                      | max   | °C              | +85          |
| <b>Dimensions</b>                    |   |                 |              |
| <b>Wiring diagrams</b>               |   |                 |              |
| <b>Certifications and compliance</b> |   |                 |              |
| Compliance                           | CSA C22.2 n° 14   |                 |              |
|                                      | IEC/EN/BS 60947-1   |                 |              |
|                                      | IEC/EN/BS 60947-5-1   |                 |              |
|                                      | UL508   |                 |              |
| Certificates                         | CCC   |                 |              |
|                                      | cULus   |                 |              |
|                                      | EAC   |                 |              |
|                                      | RINA  |                 |              |
|                                      | UL  |                 |              |
| <b>ETIM classification</b>           |   |                 |              |
| ETIM 8.0                             | EC000204 - Lamp holder block for control circuit devices    |                 |              |