

Product designation	Miniature circuit breaker (MCB)		
Product type designation	P1 MB		
Number of DIN modules	2		
Compliance	IEC / UL1077		
Electrical features			
Rated insulation voltage U_i IEC/EN	V	440	
Rated impulse withstand voltage U_{imp}	kV	4	
Rated operational voltage AC (IEC)	VAC	230/400	
Rated operational voltage DC	VDC	80	
Rated frequency	Hz	50/60	
Rated current (I_n)	A	16	
Tripping curve	C		
Short circuit rating (IEC)	kA	10	
Power dissipation per pole max	W	1.69	
Ambient conditions			
Operating temperature	min	°C	-40
	max	°C	+70
Storage temperature	min	°C	-40
	max	°C	+80
Max altitude	m	2000	
Mechanical features			
Operating position	normal		Vertical plan
			35mm DIN rail
Fixing	35mm DIN rail		
Tightening torque for terminals	min	Nm	1.8
	max	Nm	2
	min	lbin	16
	max	lbin	17.7
Terminals tool	Pz 2		
Conductor section	IEC		
	min	mm ²	1
	max	mm ²	35
	AWG/Kcmil		
min		14	
max		6	
Weight	g		230
Frontal IP degree	IP20		
Pollution degree	2		
Dimensions			
Wiring diagrams			
Certifications and compliance			
Compliance	CSA C22.2 n°235. UR "UL Recognized" per Canada e USA.		
	IEC/EN 60898-1		
	IEC/EN 60947-2		
	UL 1077		
Certifications			

cURus

EAC

TÜV-Rheinland

ETIM classification

ETIM 8.0

EC000042 -
Miniature circuit
breaker (MCB)