

Product designation				Power contactor
Product type designation				BF50
Contact characteristics				
Number of poles	Nr.			3
Rated insulation voltage U _i IEC/EN	V			1000
Rated impulse withstand voltage U _{imp}	kV			8
Operational frequency	min	Hz	25	
	max	Hz	400	
IEC Conventional free air thermal current I _{th}	A			90
Operational current I _e	AC-1 (≤40°C)	A	90	
	AC-1 (≤55°C)	A	75	
	AC-1 (≤70°C)	A	65	
	AC-3 (≤440V ≤55°C)	A	50	
	AC-4 (400V)	A	28	
Rated operational power AC-3 (T≤55°C)	230V	kW	15	
	400V	kW	22	
	415V	kW	30	
	440V	kW	30	
	500V	kW	30	
	690V	kW	37	
	1000V	kW	22	
Rated operational power AC-1 (T≤40°C)	230V	kW	34	
	400V	kW	59	
	500V	kW	74	
	690V	kW	102	
IEC max current I _e in DC1 with L/R ≤ 1ms with 1 poles in series	≤24V	A	45	
	48V	A	40	
	75V	A	40	
	110V	A	8	
	220V	A	–	
IEC max current I _e in DC1 with L/R ≤ 1ms with 2 poles in series	≤24V	A	60	
	48V	A	60	
	75V	A	60	
	110V	A	50	
	220V	A	7	
IEC max current I _e in DC1 with L/R ≤ 1ms with 3 poles in series	≤24V	A	60	
	48V	A	60	
	75V	A	60	
	110V	A	55	
	220V	A	75	
IEC max current I _e in DC1 with L/R ≤ 1ms with 4 poles in series	≤24V	A	60	
	48V	A	60	
	75V	A	60	
	110V	A	60	
	220V	A	90	

IEC max current I_e in DC3-DC5 with L/R ≤ 15ms with 1 poles in series

≤24V	A	30
48V	A	25
75V	A	22
110V	A	3
220V	A	–

IEC max current I_e in DC3-DC5 with L/R ≤ 15ms with 2 poles in series

≤24V	A	35
48V	A	35
75V	A	30
110V	A	25
220V	A	5

IEC max current I_e in DC3-DC5 with L/R ≤ 15ms with 3 poles in series

≤24V	A	50
48V	A	50
75V	A	45
110V	A	30
220V	A	40

IEC max current I_e in DC3-DC5 with L/R ≤ 15ms with 4 poles in series

≤24V	A	55
48V	A	55
75V	A	55
110V	A	45
220V	A	50

Short-time allowable current for 10s (IEC/EN60947-1)

A	400
---	-----

Protection fuse

gG (IEC)	A	100
aM (IEC)	A	50

Making capacity (RMS value)

A	500
---	-----

Breaking capacity at voltage

440V	A	400
500V	A	352
690V	A	312

Resistance per pole (average value)

mΩ	0.8
----	-----

Power dissipation per pole (average value)

I _{th}	W	6.5
AC3	W	2

Tightening torque for terminals

min	Nm	4
max	Nm	5
min	I _{bin}	2.95
max	I _{bin}	3.69

Tightening torque for coil terminal

min	Nm	0.8
max	Nm	1
min	I _{bin}	Prodotti finiti
max	I _{bin}	Prodotti finiti

Max number of wires simultaneously connectable

Nr.	2
-----	---

Conductor section

Flexible w/o lug conductor section

min	mm ²	1.5
max	mm ²	35

Flexible c/w lug conductor section

	min	mm ²	1.5
	max	mm ²	35
Power terminal protection according to IEC/EN 60529			IP20 front
Mechanical features			
Operating position			
	normal allowable		Vertical plan ±30°
Fixing			Screw / DIN rail 35mm
Weight		g	1060
Operations			
Mechanical life		cycles	15000000
Electrical life		cycles	1400000
Safety related data			
Performance level B10d according to EN/ISO 13489-1			
	rated load mechanical load	cycles cycles	1400000 15000000
Mirror contacts according to IEC/EN 60947-4-1			Yes
EMC compatibility			Yes
AC coil operating			
Rated AC voltage at 50/60Hz, 60Hz			
	min	V	20
	max	V	48
Rated AC voltage at 50/60Hz			V 24
AC operating voltage			
	of 50/60Hz coil powered at 50Hz drop-out	max	%Us ≤70 Us min
	of 50/60Hz coil powered at 60Hz pick-up	min	%Us 80 Us min
		max	%Us 110 Us max
	drop-out	max	%Us ≤70 Us min
AC average coil consumption at 20°C			
	of 50/60Hz coil powered at 50Hz	in-rush holding	VA 35...120 VA 1.5...3.7
	of 50/60Hz coil powered at 60Hz	in-rush holding	VA 35...120 VA 1.5...3.7
Dissipation at holding ≤20°C 50Hz			W 1...2.5
DC coil operating			
DC rated control voltage			
	min	V	20
	max	V	48
DC rated control voltage			V 24
DC operating voltage			
	pick-up	min	%Us 85 Us min
		max	%Us 110 Us max
	drop-out	max	%Us ≤70 Us min

Average coil consumption $\leq 20^{\circ}\text{C}$

in-rush	W	23...68
holding	W	1.2...1,9

Max cycles frequency

Mechanical operation cycles/h 1500

Operating times

Average time for U_s control

in AC

Closing NO

min	ms	12
max	ms	28

Opening NO

min	ms	8
max	ms	22

in DC

Closing NO

min	ms	40
max	ms	85

Opening NO

min	ms	20
max	ms	55

UL technical data

Full-load current (FLA) for three-phase AC motor

at 480V	A	52
at 600V	A	41

Yielded mechanical performance

for single-phase AC motor

110/120V	HP	5
230V	HP	10

for three-phase AC motor

200/208V	HP	15
220/230V	HP	20
460/480V	HP	40
575/600V	HP	40

General USE

Contactor

AC current	A	90
------------	---	----

Short-circuit protection fuse, 600V

High fault

Short circuit current	kA	100
Fuse rating	A	150
Fuse class		J

Standard fault

Short circuit current	kA	5
Fuse rating	A	150
Fuse class		RK5

Ambient conditions

Temperature

Operating temperature

min	$^{\circ}\text{C}$	-40
max	$^{\circ}\text{C}$	70

Storage temperature

min	$^{\circ}\text{C}$	-50
max	$^{\circ}\text{C}$	80

Max altitude	m	3000
Resistance & Protection		
Pollution degree		3
Dimensions		
Wiring diagrams		
Certifications and compliance		
Compliance	CSA C22.2 n° 60947-1 CSA C22.2 n° 60947-4-1 IEC/EN 60947-1 IEC/EN 60947-4-1 UL 60947-1 UL 60947-4-1	
Certificates	CCC cULus	
ETIM classification		
ETIM 8.0		EC000066 - Power contactor, AC switching