

Product designation	Miniature circuit breaker (MCB)			
Product type designation	P2 MB			
Number of DIN modules	1.5			
Compliance	IEC / UL1077			
Electrical features				
Rated insulation voltage U_i IEC/EN	V	400		
Rated impulse withstand voltage U_{imp}	kV	6		
Rated operational voltage AC (IEC)	VAC	230/400		
Rated frequency	Hz	50/60		
Rated current (I_n)	A	100		
Tripping curve	C			
Short circuit rating (IEC)	kA	10		
Power dissipation per pole max	W	14		
Ambient conditions				
Operating temperature	min	°C	-40	
	max	°C	+70	
Storage temperature	min	°C	-40	
	max	°C	+80	
Max altitude	m	2000		
Mechanical features				
Operating position	normal		Vertical plan	
			35mm DIN rail	
Fixing	35mm DIN rail			
Tightening torque for terminals	min	Nm	3.2	
	max	Nm	3.5	
	min	Ibin	28.3	
	max	Ibin	31	
Terminals tool	Pz 2			
Conductor section	IEC	min	mm ²	2.5
		max	mm ²	50
	AWG/Kcmil	min	14	
		max	1/0	
Weight	g		166	
Frontal IP degree	IP20			
Pollution degree	3			
Dimensions				
Wiring diagrams				
Certifications and compliance				
Compliance	CSA C22.2 n°235. UR "UL Recognized" per Canada e USA.			
	IEC/EN 60947-2			
	UL 1077			
Certifications	cURus			
	EAC			

TÜV-Rheinland

ETIM classification

ETIM 8.0

EC000042 -
Miniature circuit
breaker (MCB)