

Product designation			Power contactor
Product type designation			BFK115
Contact characteristics			
Number of poles	Nr.	3	
Rated insulation voltage Ui IEC/EN	V	690	
Rated impulse withstand voltage Uimp	kV	8	
Operational frequency	min	Hz	25
	max	Hz	400
IEC Conventional free air thermal current Ith	A	160	
Rated operational power AC-6b (T≤40°C)	230V	kvar	45
	400V	kvar	75
	440...480V	kvar	85
	690V	kvar	135
Short-time allowable current for 10s (IEC/EN60947-1)	A	920	
Protection fuse	gG (IEC)	A	160
		A	1500
Making capacity (RMS value)		A	1500
Breaking capacity at voltage	440V	A	1200
	500V	A	850
	690V	A	905
Resistance per pole (average value)	mΩ	0.45	
Power dissipation per pole (average value)	Ith	W	11.5
Tightening torque for terminals	min	Nm	6
	max	Nm	7
	min	Ibin	4.4
	max	Ibin	5.2
Tightening torque for coil terminal	min	Nm	0.8
	max	Nm	1
	min	Ibin	Prodotti finiti
	max	Ibin	Prodotti finiti
Max number of wires simultaneously connectable	Nr.	2	
Conductor section			
Flexible w/o lug conductor section	min	mm²	1.5
	max	mm²	70
Flexible c/w lug conductor section	min	mm²	1.5
	max	mm²	70
Power terminal protection according to IEC/EN 60529		IP20 front	
Mechanical features			
Operating position	normal	Vertical plan	
	allowable	±30°	
Fixing		Screw / DIN rail 35mm	
Weight	g	2095	
Operations			

Mechanical life	cycles	15000000
Electrical life	cycles	1200000

Safety related data

Performance level B10d according to EN/ISO 13489-1

rated load	cycles	400000
mechanical load	cycles	15000000

EMC compatibility

Rated AC voltage at 60Hz

AC coil operating

AC operating voltage

of 60Hz coil powered at 60Hz

pick-up

min	%Us	80
max	%Us	110
min	%Us	20
max	%Us	55

Max cycles frequency

Mechanical operation

cycles/h 1500

Operating times

Average time for Us control

in AC

Closing NO

min	ms	16
max	ms	32

Opening NO

min	ms	9
max	ms	24

UL technical data

General USE

Contactor

AC current	A	160
------------	---	-----

Ambient conditions

Temperature

Operating temperature

min	°C	-50
max	°C	70

Storage temperature

min	°C	-60
max	°C	80

Max altitude

m	3000
---	------

Resistance & Protection

Pollution degree

3

Dimensions

Wiring diagrams

Certifications and compliance

Compliance

CSA C22.2 n° 60947-1

CSA C22.2 n° 60947-4-1

IEC/EN 60947-1

IEC/EN 60947-4-1

UL 60947-1

UL 60947-4-1

Certificates	
	CCC
	cULus
ETIM classification	
ETIM 8.0	EC001079 - Capacitor contactor