

Product designation				RF110
Product type designation				Motor protection relay
General characteristics				
Number of poles		Nr.	3	
Overvoltage category				III
Pollution degree				3
Frontal IP degree				IP20
Type of release				Thermal
Protection fuse				
	gG (IEC)	A	200	
	aM (IEC)	A	125	
	K5 (UL)	A	350	
Phase failure detection				Yes
Reset mode				Manual
Power circuit characteristics				
Rated insulation voltage U_i IEC/EN		V	690	
Rated impulse withstand voltage U_{imp}		kV	8	
Rated operational voltage		V	690	
Operational frequency				
		min	Hz	0
		max	Hz	400
Operational current I_e				
		Operational current min	A	90
		Operational current max	A	110
Tripping class				10A
Test Button				Yes
Trip indicator				Yes
Terminals				
		type	Yoke clamp	
		screw	M5	
		width	mm	9
		tool	Phillips 2	
Tightening torque for terminals				
		min	Nm	3.9
		max	Nm	3.9
		min	lbin	2.88
		max	lbin	2.88
Conductor section				
		AWG/kcmil max	2	
Auxiliary circuit characteristics				
Auxiliary contacts				
		NO	Nr.	1
		NC	Nr.	1
Auxiliary Rated insulation voltage U_i IEC/EN		V	690	
Auxiliary Rated impulse withstand voltage U_{imp}		kV	6	
Auxiliary Rated operational voltage		V	690	
Operating current AC15				
		24V	A	1.5
		120V	A	1.5
		240V	A	0.75
		500V	A	0.72
Operating current DC13				

	125V	A	0.11
	600V	A	0.22
IEC Conventional free air thermal current I _{th}		A	10
Terminals			
	Auxiliary circuit type		Screw and washer
	Auxiliary circuit screw		M3,5
	Auxiliary circuit width	mm	8
	Auxiliary circuit tool		Phillips 1
Conductor section			
	Auxiliary circuit Flexible w/o lug max	mm ²	2.5
	Auxiliary circuit Flexible c/w lug max	mm ²	2.5
Tightening torque for terminals			
	Auxiliary circuit min	Nm	1
	Auxiliary circuit max	Nm	1
	Auxiliary circuit min	lbin	0.74
	Auxiliary circuit max	lbin	0.74
UL/CSA and IEC/EN 60947-5-1 designation			B600-P600
Ambient conditions			
Operating temperature			
	min	°C	-20
	max	°C	55
Storage temperature			
	min	°C	-55
	max	°C	80
Compensation temperature			
	min	°C	-15
	max	°C	55
Max altitude		m	3000
Mechanical features			
Operating position			
	normal allowable		Vertical plan ±30°
Fixing			Direct mounting on BF95 - BF150
Weight		g	365
UL technical data			
Full-load current (FLA) for three-phase AC motor			
	at 480V	A	110
	at 600V	A	110
Dimensions			
Wiring diagrams			
Certifications and compliance			
Compliance			
	CSA C22.2 n° 14		
	IEC/EN 60947-1		
	IEC/EN 60947-4-1		
	UL508		
Certifications			
	cULus		
ETIM classification			

ETIM 8.0

EC000106 -
Thermal overload
relay