



RF82  
Motor protection  
relay

Product designation

Product type designation

**General characteristics**

Number of poles	nr.	3
Overvoltage category		III
Pollution degree		3
Frontal IP degree		IP20
Type of release		Thermal
Protection fuse		
	gG (IEC)	A 80
	aM (IEC)	A 50
	K5 (UL)	A 150
Phase failure detection		yes
Reset mode		Manual

**Power circuit characteristics**

Rated insulation voltage $U_i$ IEC/EN	V	690
Rated impulse withstand voltage $U_{imp}$	kV	8
Rated operational voltage	V	690
Operational frequency		
	min	Hz 0
	max	Hz 400
Operational current $I_e$		
	Operational current min	A 28
	Operational current max	A 42
Tripping class		10A
Test Button		yes
Trip indicator		yes

Terminals

type	Yoke clamp
screw	M5
width	mm 9
tool	Phillips 2

Tightening torque for terminals

min	Nm	3.9
max	Nm	3.9
min	lbin	2.88
max	lbin	2.88

Conductor section

AWG/kcmil max	2
---------------	---

**Auxiliary circuit characteristics**


Auxiliary contacts

NO	nr.	1
NC	nr.	1


Auxiliary Rated insulation voltage  $U_i$  IEC/EN

V	690
---	-----

Auxiliary Rated impulse withstand voltage Uimp		kV	6
Auxiliary Rated operational voltage		V	690
Operating current AC15	24V	A	3
	120V	A	3
	240V	A	1.5
	380V	A	0.95
	480V	A	0.75
	500V	A	0.72
Operating current DC13	600V	A	0.6
	125V	A	0.11
	600V	A	0.22
Conventional free air thermal current Ith IEC/EN		A	10
<b>Terminals</b>			
	Auxiliary circuit type		Screw and washer
	Auxiliary circuit screw		M3,5
	Auxiliary circuit width	mm	8
	Auxiliary circuit tool		Phillips 1
<b>Conductor section</b>			
	Auxiliary circuit Flexible w/o lug max	mm <sup>2</sup>	2.5
	Auxiliary circuit Flexible c/w lug max	mm <sup>2</sup>	2.5
<b>Tightening torque for terminals</b>			
	Auxiliary circuit min	Nm	1
	Auxiliary circuit max	Nm	1
	Auxiliary circuit min	Ibin	0.74
	Auxiliary circuit max	Ibin	0.74
UL/CSA and IEC/EN 60947-5-1 designation			B600-P600
<b>Ambient conditions</b>			
<b>Operating temperature</b>			
	min	°C	-20
	max	°C	55
<b>Storage temperature</b>			
	min	°C	-55
	max	°C	80
<b>Compensation temperature</b>			
	min	°C	-15
	max	°C	55
Max altitude		m	3000
<b>Mechanical features</b>			
<b>Operational position</b>			
	Operating position normal		Vertical plan
	Operating position allowable		±30°
Weight		g	365
<b>UL technical data</b>			
<b>Full-load current (FLA) for three-phase AC motor</b>			
	at 480V	A	42
	at 600V	A	42
<b>Dimensions</b>			



**Wiring diagrams**



**Certifications and compliance**

**Compliance**

CSA C22.2 n° 14

IEC/EN 60947-1

IEC/EN 60947-4-1

UL508

**Certifications**

cULus