

Product designation				RFNA82
Product type designation				Motor protection relay
<b>General characteristics</b>				
Number of poles		Nr.	3	
Overvoltage category				III
Pollution degree				3
Frontal IP degree				IP20
Type of release				Thermal
Protection fuse				
	gG (IEC)	A	125	
	aM (IEC)	A	80	
	K5 (UL)	A	200	
Phase failure detection				No
Reset mode				Automatic
<b>Power circuit characteristics</b>				
Rated insulation voltage $U_i$ IEC/EN		V	690	
Rated impulse withstand voltage $U_{imp}$		kV	8	
Rated operational voltage		V	690	
Operational frequency				
		min	Hz	0
		max	Hz	400
Operational current $I_e$				
	Operational current min	A	46	
	Operational current max	A	65	
Tripping class				10A
Test Button				Yes
Trip indicator				Yes
Terminals				
		type	Yoke clamp	
		screw	M5	
		width	mm	9
		tool	Phillips 2	
Tightening torque for terminals				
		min	Nm	3.9
		max	Nm	3.9
		min	lbin	2.88
		max	lbin	2.88
Conductor section				
		AWG/kcmil max	2	
<b>Auxiliary circuit characteristics</b>				
Auxiliary contacts				
	NO	Nr.	1	
	NC	Nr.	1	
Auxiliary Rated insulation voltage $U_i$ IEC/EN		V	690	
Auxiliary Rated impulse withstand voltage $U_{imp}$		kV	6	
Auxiliary Rated operational voltage		V	690	
Operating current AC15				
	24V	A	1.5	
	120V	A	1.5	
	240V	A	0.75	
IEC Conventional free air thermal current $I_{th}$		A	10	
Terminals				

	Auxiliary circuit type		Screw and washer
	Auxiliary circuit screw		M3,5
	Auxiliary circuit width	mm	8
	Auxiliary circuit tool		Phillips 1
Conductor section			
	Auxiliary circuit Flexible w/o lug max	mm <sup>2</sup>	2.5
	Auxiliary circuit Flexible c/w lug max	mm <sup>2</sup>	2.5
Tightening torque for terminals			
	Auxiliary circuit min	Nm	1
	Auxiliary circuit max	Nm	1
	Auxiliary circuit min	lbin	0.74
	Auxiliary circuit max	lbin	0.74
UL/CSA and IEC/EN 60947-5-1 designation			C300-R300
<b>Ambient conditions</b>			
Operating temperature			
	min	°C	-20
	max	°C	55
Storage temperature			
	min	°C	-55
	max	°C	80
Compensation temperature			
	min	°C	-15
	max	°C	55
Max altitude		m	3000
<b>Mechanical features</b>			
Operating position			
	normal allowable		Vertical plan ±30°
Fixing			Direct mounting on BF40 - BF94
Weight		g	365
<b>UL technical data</b>			
Full-load current (FLA) for three-phase AC motor			
	at 480V	A	65
	at 600V	A	65
<b>Dimensions</b>			
<b>Wiring diagrams</b>			
<b>Certifications and compliance</b>			
Compliance			
	CSA C22.2 n° 14		
	IEC/EN 60947-1		
	IEC/EN 60947-4-1		
	UL508		
Certifications			
	cULus		
<b>ETIM classification</b>			
ETIM 8.0			EC000106 - Thermal overload relay