

Product designation				Fuse holder	□
Product type designation				FB	
Number of DIN modules				2	
Operating voltage type				AC	
<b>Electrical features</b>					
IEC Utilization category				AC22B 500V -	AC21B 690V
Derating factor of rated current $I_n$ for different ambient temperature					
	20°C			1	
	30°C			0.95	
	40°C			0.9	
	50°C			0.8	
	60°C			0.7	
	70°C			0.5	
Derating factor of rated current $I_n$ for side by side fuse holders (poles)					
	1-4			1	
	5-6			0.8	
	7-9			0.7	
	≥10			0.6	
Rated current ( $I_n$ )		A		32	
<b>Ambient conditions</b>					
Operating temperature					
	min	°C		-20	
	max	°C		+70	
Storage temperature					
	min	°C		-40	
	max	°C		+80	
Max altitude			m	3000	
<b>Mechanical features</b>					
Operating position					
	normal			Vertical plan	
	allowable			Any	
Fixing				35mm DIN rail	
Tightening torque for terminals					
	max	Nm		2.5	
	max	lbin		22	
Conductor section					
	Flexible max (IEC)	mm <sup>2</sup>		16	
	- Flexible max (AWG/kcmil)			8	
	Rigid max (IEC)	mm <sup>2</sup>		16	
	- Rigid max (AWG/kcmil)			8	
Weight			g	134	
<b>Resistance &amp; Protection</b>					
Frontal IP degree				IP20	
<b>Dimensions</b>					
<b>Wiring diagrams</b>					
<b>Certifications and compliance</b>					
Compliance	CSA C22.2 n°4248.1				
	IEC/EN 60269-1				
	IEC/EN 60269-2				
	IEC/EN 60947-1				

FUSE HOLDER UL RECOGNIZED AND CSA CERTIFIED, FOR 10X38MM FUSES. 32A RATED CURRENT AT 690VAC, 1P+N. WITHOUT STATUS INDICATOR. 2 MODULES

---

IEC/EN 60947-3

---

UL 4248-1

Certifications

---

cURus

---

EAC

ETIM classification

ETIM 8.0

EC002705 -  
Holder for  
cylindrical fuse