



D'Gel

Cable Gel Solvent



FEATURES

- Safe on cable insulation and components, metals, and most plastics
- Preferred by Telecom workers
- Removes petroleum, polyethylene, and silicone based gels
- Rinses off with water and contains no chlorinated solvents
- Removes cable gels, blocking compounds, flooding and filling compounds, grease, tar, and oil
- Flash point above 140°F (60°C)
- Bellcore tested for complete compatibility with telco components

APPLICATIONS

- Blocking Compounds
- Equipment
- Filling Compounds
- Forming Compounds
- Copper Cables
- Equipment
- Fiber Optic Cables
- Flooding Compounds
- Grease
- Removing Cable Gels
- Resin
- Tar
- Tools
- Wax
- Painted Surfaces
- Oil

SPECIFICATIONS AND APPROVALS

- Bellcore

PROPERTIES

Appearance/physical state	Liquid
Odor	Orange (Citrus)
Melting point/freezing point	N/A
Boiling point/range	379.4°F (193°C) @ 760mmHg
Vapor pressure	N/A
Partition coefficient	<1
Percent volatile	97%
Flammability limit	Lower: 1.3%; Upper: 8.9%
Color	Colorless
Flash point	161.60°F (72.00°C) (TCC)
Relative density	N/A
Evaporation rate	< 10 (BuAc = 100)
Vapor density	> 1 (air = 1)
Auto-ignition temperature	N/A
Viscosity	< 3 cSt @ 25°C
Specific Gravity (water=1)	0.78 - 0.8 @ 20°C

DIRECTIONS

Apply to the cable using a saturated cloth, towel, or brush. Wipe towards the conductor. Allow the D'Gel solvent to evaporate (air dry) or wipe dry with a line free cloth. Soaking the cable may be desirable in some situations.

HANDLING

Wash thoroughly after handling. Use only outdoors or in a well-ventilated area. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves/protective clothing/eye protection/face protection.

STORAGE

Keep cool. Store in a well-ventilated place. Keep container tightly closed. Store locked up.

DISPOSAL INFORMATION

Dispose of content/container in accordance with local/regional/national/international regulations

AVAILABLE PRODUCTS

Part No.		Net Contents	Container Type	Units/Case	Case Weight
US	Canada				
61201		1 gal / 3.78 L	can	4	32 lbs
61232		32 fl oz / 946 mL	bottle	12	22 lbs
61244		1 wipe	packet	144	6 lbs
61255	C61255	55 gal / 208 L	drum	1	380 lbs
61296	C61296	3 qts / 946 mL	pail	4	23 lbs



CONTACT YOUR ITW PRO BRANDS REPRESENTATIVE TODAY!

800.241.8334 | www.itwprobrands.com

LPS®, SCRUBS®, DYKEM®, Accu-Lube®, DYMOM®, Spray Nine®, and Cedar® are registered trademarks and Rustlick™, Diamondkote™, and MetalMates™ are trademarks of Illinois Tool Works • All Rights Reserved