



S4906WB

Omnidirectional Antenna 4900-5875 MHz

The wideband S4906WB is one in a series of omni antennas that have been optimized for direct chassis mount to outdoor radios or NEMA enclosures. These antennas come standard with an integrated N male or female connector directly mounted to the base of the antenna. The rugged directly mounted connector is perfect for outdoor MESH applications that often require the antenna to be directly mounted to the radio or enclosure. The antenna is enclosed in a UV stable, water-resistant housing and the antenna will provide years of trouble-free service. The antenna series includes antennas of various gains all with integrated N male or female connectors. There is a mast mount hardware kit available for applications that require the antenna to be remotely mounted from the radio enclosure.

FEATURES AND BENEFITS

- Vertically polarized omnidirectional
- Rugged, lightweight, and water resistant
- Direct to radio mounting
- 5 GHz broadband WLAN

APPLICATIONS

- College campuses
- Airports
- Hospitals
- Transportation centers
- WiMAX

ELECTRICAL SPECIFICATION

Model Name	S4906WB
Operating Frequency (MHz)	4900-5875
VSWR - Max	2.0:1
Gain (dBi)	8.0
Nominal Impedance (Ohms)	50
Max Power - Ambient 25°C (W)	10
Polarization	Vertical linear
Vertical Plane 3 dB Beamwidth	16°
Horizontal Plane 3 dB Beamwidth	Omnidirectional



MECHANICAL SPECIFICATION

Dimensions - mm (inches)	292.1 x 25.4 (11.5 x 1.0)
Weight - kg (lbs.)	0.17 (0.37)
Radome Material	White UV polycarbonate
Connector	Type N male female
Mount Style	Direct mount (upright or inverted)

ENVIRONMENTAL SPECIFICATION

Operating Temperature - °C (°F)	-30 to +65°C (-22 to +149°F)
Storage Temperature - °C (°F)	-40 to +80°C (-40 to +176°F)
Wind Operational - km/hr (mph)	161(100)
Wind Survival - km/hr (mph)	219 (136)
Ingress Protection Rating	IP54
Material Substance Compliance	RoHS

RADIATION PATTERNS



TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, complete, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE EXPRESSLY DISCLAIMS ALL IMPLIED WARRANTIES REGARDING THE INFORMATION CONTAINED HEREIN, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. In no event will TE be liable for any direct, indirect, incidental, special or consequential damages arising from or related to recipient's use of the information. It is the sole responsibility of recipient of this information to verify the results of this information using their engineering and product environment. Recipient assumes any and all risks associated with the use of the information. Antenna performance may vary. TE is a component manufacturer, and customer and/or end-user is responsible for all end-use compliance and regulatory requirements.

©2025 TE Connectivity. All Rights Reserved.

05/25 Original