


Product Details for 132 -0112 -0003



132 -0112 -0003

Tyco Part Number: 4 - 1532005 - 4

[Active](#)

SMB RF Connectors

[RoHS Compliant](#) (Statement of Compliance)

Product Highlights:

- ? Connector
- ? Plug
- ? Miniature
- ? Terminate To Coaxial Cable
- ? Coupler Style = Threaded

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [132 -0112 -000X=PLUG ASSY NON -ENVIRONMENTAL GOLDEN CRI...](#) (TIF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? [Golden Crimp and Crimp Silver Connectors](#) (PDF, English)

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Gender](#) = Plug
- ? Connector Series = Miniature
- ? [Body Style](#) = Straight
- ? [Grade](#) = Commercial
- ? Safety Wire Holes = Without
- ? Thread Size = 4.83 [.190] -32 UNF -2B
- ? Body Material = Brass
- ? Coupling Nut Style = Full Hex
- ? Dielectric Material = TEFLON

Mechanical Attachment:

- ? [Panel Attachment](#) = Without

Electrical Characteristics:

- ? [Connector Impedance \(?\)](#) = 50
- ? Environmental Seal = Without
- ? Solderless = Yes

Termination Related Features:

- ? [Coaxial Cable Termination Type](#) = Crimp

Body Related Features:

- ? Coupler Style = Threaded
- ? [Pin Protection](#) = Without
- ? Solder Lug = Without
- ? [Body Plating](#) = Gold per MIL -G-45204, Type II, Grade C, Class 1
- ? Cable Jacket Diameter (mm [in]) = 2.24 [0.088]

Contact Related Features:

- ? [Center Contact Plating](#) = Gold per MIL -G-45204, Type II, Grade C, Class 1
- ? Contacts = With

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Coaxial Cable

Other:

- ? Brand = Microdot