P1MB2PB40

MINIATURE CIRCUIT BREAKER, 2P - 10KA. 2 MODULES, CHARACTERISTIC B, 40A

Product designation			Miniature circuit breaker (MCB)
Product type designation			P1 MB
Number of DIN modules			2
Compliance			IEC / UL1077
Electrical features			
Rated insulation voltage Ui IEC/EN		V	440
Rated impulse withstand voltage Uimp		kV	4
Rated operational voltage AC (IEC)		VAC	230/400
Rated operational voltage DC		VDC	80
Rated frequency		Hz	50/60
Rated current (In)		A	40
Tripping curve			B
Short circuit rating (IEC)		kA	10
Power dissipation per pole max		W	3.84
Ambient conditions			
Operating temperature			
	min	°C	-40
	max	°C	+70
Storage temperature			
	min	°C	-40
	max	°C	+80
Max altitude		m	2000
Mechanical features			
Operating position			
	normal		Vertical plan
Fixing			35mm DIN rail
Tightening torque for terminals			
	min	Nm	1.8
	max	Nm	2
	min	lbin	16
	max	lbin	17.7
Terminals tool			Pz 2
Conductor section			
IEC			
	min	mm²	1
	max	mm²	35
AWG/Kcmil			
	min		14
	max		6
Weight		g	230
Frontal IP degree			IP20
Pollution degree			2
Dimensions			
Wiring diagrams			
Certifications and compliance			
Compliance			
CSA C22.2 n°235. UR “UL Recognized” per Canada e USA.			
IEC/EN 60898-1			
IEC/EN 60947-2			
UL 1077			
Certifications			

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding

	cURus
	EAC
	TÜV-Rheinland

ETIM classification

ETIM 8.0	EC000042 - Miniature circuit breaker (MCB)

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding