

# Product data sheet

Specifications



## Hermetically sealed plug-in relays, SE Relays, 3A, 4 CO, 6VDC

782DXDH10-6D

**Product availability: Non-Stock - Not normally stocked in distribution facility**

### Main

Range of Product	Harmony Electromechanical Relays
Series name	782H series
Product or Component Type	Plug-in relay
Contacts type and composition	4 C/O
Relay Type	Hermetically sealed relay
Status LED	Without
[Uc] control circuit voltage	6 V DC
cover options	Hermetically sealed
[Ithe] conventional enclosed thermal current	3 A
Local signalling	Without LED without lockable test button

### Complementary

class number	782H
Minimum switching current	100 mA 12 V AC 100 mA 12 V DC
Electrical durability	100000 cycles resistive IEC
Dielectric strength	1600 V AC between coil and contact 1600 V AC between poles
Control Type	Without lockable test button
Coil resistance	40 Ohm
Average coil consumption	0.90 W
Response Time	20 ms
Associated fuse rating	6 A gG at 400 V coordination type 2 for power circuit
Short-circuit current	1 kA
Average pole impedance	2 mOhm
Maximum switching voltage	240 V AC
[Ie] rated operational current	3 A at 120 V AC (on resistive load) 3 A at 240 V AC (on resistive load) 3 A at 30 V DC (on resistive load)
Mechanical durability	10000000 cycles
Contacts material	Gold flashed fine silver
Shape of pin	Flat (faston type)
Width	0.90 in (22.75 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Height</b>	1.3 in (32.5 mm)
<b>Depth</b>	1.13 in (28.75 mm)
<b>Net Weight</b>	1.6 oz (45 g)

## Environment

<b>Shock resistance</b>	10 gn
<b>Vibration resistance</b>	6 gn 10...55 Hz)
<b>Environmental characteristic</b>	Hazardous location T5 70 °C
<b>Product Certifications</b>	UL CSA CE
<b>Ambient Air Temperature for Storage</b>	-76...185 °F (-60...85 °C)
<b>Ambient Air Temperature for Operation</b>	-49...158 °F (-45...70 °C)

## Ordering and shipping details

<b>Category</b>	US10CP221127
<b>Discount Schedule</b>	0CP2
<b>GTIN</b>	3606481108319
<b>Returnability</b>	No
<b>Country of origin</b>	CN

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	1.13 in (2.875 cm)
<b>Package 1 Width</b>	0.90 in (2.275 cm)
<b>Package 1 Length</b>	1.13 in (2.875 cm)
<b>Package 1 Weight</b>	1.6 oz (45 g)
<b>Unit Type of Package 2</b>	CAR
<b>Number of Units in Package 2</b>	100
<b>Package 2 Height</b>	7.09 in (18 cm)
<b>Package 2 Width</b>	10.16 in (25.8 cm)
<b>Package 2 Length</b>	13.19 in (33.5 cm)
<b>Package 2 Weight</b>	11.9 lb(US) (5.4 kg)

## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

[Environmental Disclosure](#)

[Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

California proposition 65

**WARNING:** This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

## Use Again

### Repack and remanufacture

[Circularity Profile](#)

[End of Life Information](#)

Take-back

No


WEEE

 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Dimensions Drawings

Dimensions

---




(A) : 0.312 (7.92) LONG #3-48 THREAD

Connections and Schema

Wiring

---



Technical Illustration

Dimensions

---




Image of product / Alternate images

Alternative

---





Image of product in real life situation

