

Product data sheet

Specifications



Power relay, SE Relays, 4PDT, 6A, 120 VAC, clear cover

792XDXC-120A

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Range	Legacy
Product Type	Relay
Switch Function	4PDT
Contact Composition	4 NO + 4 NC

Complementary

Input Current	6 A
Contacts Material	Silver with gold flashed contacts
Local Signalling	Flag
Minimum Switching Current	10 mA 17 V
Coil Resistance	3630 Ohm
Input voltage	120 V AC
Drop-out Voltage Threshold	$\geq 0.15 U_c$ AC $\geq 0.1 U_c$ DC
Rated Operational Current	6 A at 277 V AC conforming to UL 8 A at 120 V AC conforming to UL 8 A at 30 V DC conforming to UL 6 A AC-1 (NO) conforming to IEC 3 A AC-1 (NC) conforming to IEC 6 A DC-1 (NO) conforming to IEC 3 A DC-1 (NC) conforming to IEC
Power consumption in VA	0.9 VA AC
Voltage Range	0.8...1.1 U_n AC/DC
Maximum Switching Voltage	300 V UL 300 V CSA 250 V IEC
Motor Power HP	0.33 hp 120 V AC 0.5 hp 277 V AC
Connections Terminals	Faston connectors
Mounting	Panel Carril DIN
Height	1.4 in (34.8 mm)
Width	0.8 in (21 mm)
Depth	1.07 in (27.2 mm)
Product Weight	1.3 oz (37 g)
Operating Time	25 ms 20 ms at maximum rated voltage

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Ambient Air Temperature for Operation	-40...131 °F (-40...55 °C)
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Product Certifications	UL CSA CE
Electrical Durability	100000 cycles resistive
Mechanical Durability	10000000 cycles
Dielectric Strength	2000 V AC between coil and contact 2000 V AC between poles 1300 V AC between contacts
Shock Resistance	10 gn in operation 30 gn not operating
Vibration Resistance	3 gn 35...150 Hz)operating +/- 1 mm 10...35 Hz)operating 5 gn 35...150 Hz)not operating +/- 1 mm 10...35 Hz)not operating
Surge Withstand Duration	1.2/50 µs

Ordering and shipping details

Category	US10CP221127
Discount Schedule	0CP2
GTIN	3606480781391
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.30 in (3.302 cm)
Package 1 Width	0.70 in (1.778 cm)
Package 1 Length	1.60 in (4.064 cm)
Package 1 Weight	1.120 oz (31.752 g)



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

[Environmental Disclosure](#)

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

REACH Regulation

[REACH Declaration](#)

California proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Use Again

Repack and remanufacture

Take-back


No

WEEE

 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.


Dimensions Drawings

Approximate Dimensions



Connections and Schema

Connections and Wiring Diagrams



NEMA
IEC