



# MAC (1/2"-20) Series Receptacles

## 2, 3, 4, 5 & 6 Conductor MAC Series Receptacles, 18/22AWG



Front Mount Receptacles | M16 & M20 Threads | 300 Volt, 4 amps | IP69 Rating




# of Poles	Male Faceview	Color Code	Rating	Wire AWG	Male Receptacles		Female Receptacles
					M16 x 1.5	M20 x 1.5	M20 x 1.5
2		1. Brown 2. Blue	300V 4A	18 AWG	MAC-2MR-M16-18	MAC-2MR-M20-18	MAC-2FR-M20-18
				22 AWG	MAC-2MR-M16	MAC-2MR-M20	MAC-2FR-M20
3		1. Green/Yellow 2. Red/Black 3. Red/White	300V 4A	18 AWG	MAC-3MR-M16-18	MAC-3MR-M20-18	MAC-3FR-M20-18
				22 AWG	MAC-3MR-M16	MAC-3MR-M20	MAC-3FR-M20
4		1. Red/Black 2. Red/White 3. Red 4. Green/Yellow	300V 4A	18 AWG	MAC-4MR-M16-18	MAC-4MR-M20-18	MAC-4FR-M20-18
				22 AWG	MAC-4MR-M16	MAC-4MR-M20	MAC-4FR-M20
5		1. Red/White 2. Red 3. Green/Yellow 4. Red/Yellow 5. Red/Black	300V 4A	18 AWG	MAC-5MR-M16-18	MAC-5MR-M20-18	MAC-5FR-M20-18
				22 AWG	MAC-5MR-M16	MAC-5MR-M20	MAC-5FR-M20
6		1. Red/White 2. Red 3. Green/Yellow 4. Red/Yellow 5. Red/Black 6. Red/Blue	300V 4A	22 AWG	MAC-6MR-M16	MAC-6MR-M20	MAC-6FR-M20


G  
Micro-AC Series (1/2"-20) Receptacles

12" leads are standard. Longer lead lengths are available, please consult the factory for part numbers.


Male M16 Receptacles



Male M20 Receptacles



Female M20 Receptacles



**Specifications:**

Shell: Clear Anodized Aluminum  
 Insulator: Polyamide  
 Wire: 18 & 22 AWG: UL Style 1007/1569, 300V  
 Contacts: Copper Alloy with Gold Plating

O-Ring: NBR  
 Jam Nut: Nickel Plated Brass  
 Temperature: -40°C to 105°C (-40°F to +221°F)