

**Electrical Utility**

- [Products](#)
- [Solutions](#)
- [Documentation & Literature](#)
- [News & Tradeshows](#)
- [Support](#)

[United States](#) > [Energy](#) > [Electrical Utility](#) > [Products](#) > [Electrical Utility Products Catalog](#) > [Heat Shrink](#) > [Dual Wall \(Adhesive Lined\)](#) > [United States](#) > [Energy](#) > [Electrical Utility](#) > [Products](#) > [Electrical Utility Products Catalog](#) > [Heat Shrink](#) > [Dual Wall \(Adhesive Lined\)](#) > 3M™ Heat Shrink Flexible Polyolefin Tubing EPS200-3/4-48"-Black-5 Pcs, 48 in length sticks, 5 pieces

- [Find An Account Rep](#)
- [Where To Buy \(Find A Distributor\)](#)
- [Contact Us](#)

## 3M™ Heat Shrink Flexible Polyolefin Tubing EPS200-3/4-48"-Black-5 Pcs, 48 in length sticks, 5 pieces

3M ID 80611473853 UPC# 00051128597248 Part Number EPS200-3/4-48"-Black-5 Pcs

Print Share



3M™ EPS-200 Heat Shrink Tubing is a dual-wall tubing that provides the advantage of integral, adhesive-lined construction. This flame-retardant tubing with a 2:1 shrink ratio, offers insulation for 600V-rated applications. The flexible polyolefin construction with an internal layer of thermoplastic adhesive offers moisture-seal protection in automotive and marine applications.

**Need Help?**

---

**Questions?** We can help  
[Contact Us](#)

- Dual-wall construction provides abrasion resistance and moisture-seal protection
- Offers the advantage of integral, adhesive-lined construction
- Protects electronic components, automotive, truck and marine wiring splices or bundling of wires
- Expanded I.D. of 3/4 in
- 4-ft stick
- Made of black flexible polyolefin
- Withstands temperatures of -67 to 230 degrees F (-55 to 110 degrees C)
- Flame-retardant tubing is rated for 600V applications
- UL Listed, SAE-AMS-DTL-23053/4, Class 2, CSA Certified and RoHS 2011/65/EU Compliant
- 5 sticks/case



**Overview**

**Documents**

3M™ Heat Shrink Tubing EPS-200 is color-coded for quick and easy identification of the wire. It provides a skintight fit and strain-relief protection of electronic components, truck wiring splices or wire bundling. This flame-retardant tubing has a heat shrinkable outer wall that is irradiation cross-linked for abrasion resistance. The tubing also maintains a high flow and has superior adhesion characteristics. When the tubing cools down, it forms a permanent, water-resistant barrier. It withstands temperatures of -67 to 230 degrees F (-55 to 110 degrees C). UL Listed, SAE-AMS-DTL-23053/4, Class 2, CSA Certified and RoHS 2011/65/EU Compliant.

**Specifications**

<b>Brand</b>	3M™
<b>Color</b>	Black
<b>Elongation</b>	450 %
<b>Family</b>	3M™ Heat Shrink EPS-200
<b>Length</b>	48 Inch
<b>Material</b>	Polyolefin
<b>Non-Corrosive</b>	Yes
<b>Size</b>	0.75 Inch
<b>Trademark</b>	3M

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

**3M Electrical Utility:** [Contact Us](#)

**3M:** [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2018. All Rights Reserved.