

Product designation	Miniature circuit breaker (MCB)		
Product type designation	P1 MB		
Number of DIN modules	1		
Compliance	IEC / UL489		
Electrical features			
Rated insulation voltage U_i IEC/EN	V	440	
Rated impulse withstand voltage U_{imp}	kV	4	
Rated operational voltage AC (IEC)	VAC	230/400	
Rated operational voltage AC (UL)	V	120	
Rated frequency	Hz	50/60	
Rated current (I_n)	A	63	
Tripping curve	D		
Short circuit rating (IEC)	kA	10	
Short circuit rating (UL)	kA	10	
Power dissipation per pole max	W	5.16	
Ambient conditions			
Operating temperature	min	°C	-40
	max	°C	+70
Storage temperature	min	°C	-40
	max	°C	+80
Max altitude	m	2000	
Mechanical features			
Operating position	normal		Vertical plan
			35mm DIN rail
Fixing			
Tightening torque for terminals	min	Nm	1.8
	max	Nm	2
	min	lbin	16
	max	lbin	17.7
Terminals tool	Pz 2		
Conductor section	IEC		
	min	mm ²	1
	max	mm ²	35
	AWG/Kcmil		
min		14	
max		6	
Weight	g		133
Frontal IP degree	IP20		
Pollution degree	2		
Dimensions			
Wiring diagrams			
Certifications and compliance			
Compliance	IEC/EN 60947-2		
	UL489		
Certifications	cULus		

EAC

ETIM classification

ETIM 8.0

EC000042 -
Miniature circuit
breaker (MCB)