



FG4505W

Omnidirectional Antenna 450-470 MHz

Fiberglass base station antennas feature industry leading design components that perform in extreme conditions. The FG4505W incorporates a collinear design that is enclosed in high density fiber glass, which is covered with a protective ultraviolet inhibiting coating. The radiating elements are carefully phased to provide maximum gain in the horizontal plane. The mounting sleeves are tuned to eliminate RF currents from the transmission line, resulting in a “cold” sleeve that allows for greater freedom in mounting. The antenna’s high quality and well-focused beam provides the best efficiency with the highest possible gain.

FEATURES AND BENEFITS

- High gain 7 dBi
- Every antenna is tested on a network analyzer before shipping to ensure the best performance
- Custom UV protection coating
- Durable gold anodized sleeve and cap with N-female connector

ELECTRICAL SPECIFICATIONS

Frequency Range (MHz)	450 - 470
VSWR	2.0:1
Peak Gain (dBi)	7
Nominal Impedance (Ohms)	50
Max Power - Ambient 25°C (W)	100
Polarization	Vertical
Elevation Beamwidth at Half-Power (Deg)	34
Azimuth Beamwidth at Half-Power (Deg)	360
Pattern	Omnidirectional

MECHANICAL SPECIFICATIONS


Dimensions - diameter x height - cm (in.)	3.33 x 193.0 (1.31 x 76)
Weight - kg (lbs.)	1.06 (2.34)
Radome Material	UV Treated Fiberglass
Color	White radome/Gold sleeve

CONFIGURATION


PART NUMBER	CABLE LENGTH	CONNECTOR	MOUNTING
FG4505W	N/A	N-Female	FM2 Optional

RADITION PATTERNS

2700 MHz



Azimuthal Pattern (Y, Z, or E-plane)



Elevation Pattern (Y, Z, or H-plane)

TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, complete, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE EXPRESSLY DISCLAIMS ALL IMPLIED WARRANTIES REGARDING THE INFORMATION CONTAINED HEREIN, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. In no event will TE be liable for any direct, indirect, incidental, special or consequential damages arising from or related to recipient's use of the information. It is the sole responsibility of recipient of this information to verify the results of this information using their engineering and product environment. Recipient assumes any and all risks associated with the use of the information. Antenna performance may vary. TE is a component manufacturer, and customer and/or end-user is responsible for all end-use compliance and regulatory requirements.

©2025 TE Connectivity. All Rights Reserved.

05/25 Original