



## OC515010H

### Omni Antenna

#### DIRECT MOUNT 10 DBI HORIZONTALLY POLARIZED OMNI

The Laird Technologies' OC515010H is a 5150-5875 MHz omnidirectional, collinear, horizontally polarized array especially designed to compliment interior or exterior mounted wireless network systems. An integrated RF connector is imbedded in the antenna base cap for direct AP mounting. Special venting permits either upright or inverted orientation in outdoor locations. The antenna may also be pole-mounted when separation from the AP is required for optimum positioning.

#### FEATURES


- Horizontally polarized omnidirectional
- Rugged, lightweight and water resistant
- Full 802.11a wide band performance
- Direct to radio mounting
- 5 GHz broad band WLAN

#### MARKETS


- College campuses
- Airports
- Hospitals
- Transportation centers

PARAMETER	SPECIFICATION
Antenna Part Number	OC515010H
Frequency Range	5150 - 5875 MHz
Gain	10 dBi
Polarization	Linear, Horizontal
VSWR	2.0:1
3 dB Beamwidth - E-plane	Omnidirectional
3 dB Beamwidth - H-plane	9.5°
RF Connector	Type N, Male or Female, Standard
Power	10 Watts
Weight	0.18 kg
Radome	Polycarbonate, UV, White
Operational Temperature	-30°C TO +70°C
Storage Temperature	-40°C TO +85°C
Mounting	Connector Fixed or Mast Mount Kit, Upright and Inverted Orientation

All antennas carry a 1-Year Warranty



**H-plane 5.5 GHz**



**E-plane 5.5 GHz**

**TE TECHNICAL SUPPORT CENTER**

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

**te.com**

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

©2021 TE Connectivity. All Rights Reserved.

12/21 Original