

PSQ24495-91NM

✓ ACTIVE

TE Internal #: PSQ24495-91NM

Panel Antenna, Dual Band, Wi-Fi, External Mount, Pole/Mast /Bracket Mount, N-type, Directional, Multiple Ports, > 6 dBi Peak Gain

[View on TE.com >](#)



Antennas



Communication Protocol: **Wi-Fi**

Mounting Location: **External**

Mounting Type: **Pole/Mast/Bracket Mount**

Frequency Category: **2400 – 5950**

Antenna Type: **Panel**

Features

Product Type Features

Antenna Termination	N-type
Antenna Product Type	Antenna

Configuration Features

Antenna Style	Panel
Mounting Location	External
Antenna Type	Panel
Band Type	Dual Band
Port Configuration	Multiple Ports

Signal Characteristics

Frequency Band	2400 – 2490 MHz, 4900 – 6000 MHz
Gain (Max)	7.7 dB
Frequency Category	2400 – 5950
Peak Gain	> 6 dBi

Mechanical Attachment

Mounting Type	Pole/Mast/Bracket Mount
---------------	-------------------------

Dimensions

Cable Length	.91 m[2.99 ft]
--------------	----------------



Operation/Application

Antenna Environment	Indoor, Outdoor
Directionality	Directional

Industry Standards

Communication Protocol	Wi-Fi
Primary Application	Wi-Fi

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	未针对中国 RoHS 符合性进行审核 Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: FEB 2026 (253) Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts





TE Part # L000684-03
PANEL,TRI-BAND,75CM, RP-SMAM, 2P



TE Part # L000962-02
PANEL,TBAND,75CM, RP-SMAM, 4PORTS



TE Part # PSQ24495-91NF
Panel,Dband,91CM,NF 2.4-6.0,5dBi,



TE Part # L000962-01
PANEL,TBAND,75CM, RP-SMAM, 2PORTS



TE Part # PSQ24495-91RSM
Panel,Dband,91,RSMAM 2.4 - 6.0,5dBi,



TE Part # L000684-04
PANEL,TRI-BAND,75CM, RP-SMAM, 4P

Customers Also Bought



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT



TE Part #CAT-D48-ST273
DEUTSCH Connector Solid Contacts




TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING

Documents

Product Drawings

Panel,Dband,91CM,NM 2.4-6.0,5dBi,

English

Datasheets & Catalog Pages

4-Port Directional Slant 45 MIMO Antenna 2400-2490 MHz / 4900-6000 MHz

English

Agency Approvals

UK Declaration of Conformity



English