


13 PAIR 28 AWG CABLE



CONSTRUCTION

Pair Component

Conductor: 28 AWG 7/36 Tin Plated Copper, 0.015 Inch Diameter
Insulation: 0.007 Inches of Polypropylene, 0.029 Inch Diameter
Pair: 2 Insulated Conductors Twisted Together

Final Assembly

Core: 4 Pairs (#1-4) Cabled Together
Layer 1: 9 Pairs (#5-13) Cabled Around Core
Buffer: Foam Polypropylene Tape
Inner Shield: Aluminum/Polyester Tape, Aluminum Side Facing Out, 25% Overlap
Outer Shield: 36 AWG Tin Plated Copper Braid, 85% Coverage
Jacket: 0.023 Inches of PVC, Color – Black
Diameter: 0.280 Inches Nominal
Print Legend (White Ink): "MADISON CABLE {Mfg Location Code}¹ (UL) TYPE CL2 75°C 28 AWG CSA AWM II A/B 75°C 300V FT4 RoHS COMPLIANT {Date Code}²"

¹ Mfg. Location Code, if applicable.
² Date code is a 4-digit code with the first 2 digits identifying the calendar week and the last 2 digits identifying the calendar year of manufacture. Example - 0206 for cable manufactured the second week of 2006.

COLOR CODE

Pair #	Conductor #1	Conductor #2
1	White/Tan	Tan/White
2	White/Brown	Brown/White
3	White/Pink	Pink/White
4	White/Orange	Orange/White
5	White/Yellow	Yellow/White

6	White/Green	Green/White
7	White/Blue	Blue/White
8	White/Violet	Violet/White
9	White/Gray	Gray/White
10	Tan/Brown	Brown/Tan
11	Tan/Pink	Pink/Tan
12	Tan/Orange	Orange/Tan
13	Tan/Yellow	Yellow/Tan

ELECTRICAL CHARACTERISTICS

Impedance:

Differential: 105 ± 10 Ohms @ TDR
Single-Ended: 68 ± 10 Ohms @ TDR

Capacitance:

Mutual: 16 pF/ft Maximum
Single-Ended: 25 pF/ft Maximum

Time Delay: 1.60 ns/ft Maximum

Time Delay Skew: 0.040 ns/ft Maximum

Differential Attenuation: 0.079 dB/ft Maximum @ 50 MHz

Conductor DC Resistance: 0.070 Ohms/ft Maximum @ 20°C

SAFETY CERTIFICATION

UL Listing: Type CL2 as specified in Article 725 of the National Electrical Code

CSA Certification: AWM II A/B 75°C 300 Volts FT4

RoHS Compliance: In Accordance to European Directive 2002/95/EC, Issue 13.2.2003



125 Goddard Memorial Drive • Worcester, MA 01603 USA
 Tel: (508) 752-2884 Toll-Free: (877) MADISON Fax: (508) 752-4230

Spec Number: 101-2076

Part Number: 26SDKLF025

Customer:

Customer #:

REVISION HISTORY

1	01/28/05	RL	Initial Release
2	10/20/05	EP	Added Part Number
3	11/08/05	EP	Revised Legend
4	02/23/07	DM	Revised Electricals, Insulation Wall/OD
5	02/10/11	EP	Add Date Code

Prepared By: E. Piekelniaik

Reviewed By: T. Grzysiewicz

B. Morissette

Page

1 of 1

Users should evaluate the suitability of this product for their application. Contact factory for latest revision of specification. Tyco Electronics reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to the Buyer.