



Date: 07/11/2008

MAIDA STYLE NUMBER D61ZOV271RA43T19

MAIDA ITEM NUMBER 01-0956

VARISTOR SPEC SHEET**Electrical Specifications**

Continuous AC Voltage	270	VAC
Continuous DC Voltage	360	VDC
Maximum DC Leakage @ 360 VDC	200	uA
Low Varistor Voltage Limit	382	VDC
High Varistor Voltage Limit	466	VDC
Nominal Varistor Voltage	424	VDC
Current for Varistor Voltage	1	mA
Maximum Clamp Voltage	710	V
Maximum Clamp Voltage Test Current	25	A
Peak Current Rating (1 Pulse)	3500	A
Peak Current Rating (2 Pulse)	2500	A
Energy Rating (8X20us)	80	J
Energy Rating (10X1000us)	80	J
Typical Capacitance	210	pF
Impulse Response Time	< 50	ns
Minimum Hipot of Coating	2500	VDC
Minimum I.R. of Coating	1000	MΩ

Thermal Specifications

Minimum Operating Temperature	-40	°C
Maximum Operating Temperature	85	°C
Varistor Voltage Temperature Coeff	-0.05	%/°C
Minimum Storage Temperature	-50	°C
Maximum Storage Temperature	125	°C
Current/Energy Derating Above 85°C	-2.5	%/°C

Notes

Lead Free - Complies with RoHS

**DEVELOPMENT COMPANY**


P.O. Box 3529

Hampton, Virginia 23663

(757) 723-0785 Fax (757) 722-1194

Physical Specifications

Lead Style	110B1N
X Nominal	0.3 in.
X Tolerance	0.03 in.
Lead Length Nominal	TAPE in.
Lead Length Tolerance	& REEL in.
Y Nominal	0.1 in.
Y Tolerance	0.03 in.
d Nominal	0.032 in.
Wire Gauge	20 AWG
Minimum Marking	Z271-43UL
Nominal Disk Size	10 mm
D Maximum	0.472 in.
T Maximum	0.257 in.
H Maximum	0.597 in.



* Contact Maida for a more detailed configuration drawing.

Safety Agency Recognitions

UL 1449 File Number	E86730
UL 1414 File Number	E38785
CSA File Number	LR33468
VDE File Number	40017480
SEV File Number	96.7 70250.01