



Microdot

TE Internal #: 1532204-2
25 Position D-Shaped Connector, Receptacle, Cable-to-Board,
Panel Mount, 1.27 mm [.05 in] Centerline, Wire & Cable, Signal
[View on TE.com >](#)

Connectors > D-Shaped Connectors



Number of Positions: 25
Connector & Housing Type: Receptacle
Connector System: Cable-to-Board
Connector Mounting Type: Panel Mount
Centerline (Pitch): 1.27 mm [.05 in]

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	25
---------------------	----

Contact Features

Contact Current Rating (Max)	3 A
Contact Options	Installed

Termination Features

Termination Method to Wire & Cable	Solder Cup
------------------------------------	------------

Mechanical Attachment

Connector Mounting Type	Panel Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	1.27 mm[.05 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application



Circuit Application	Signal
---------------------	--------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Cd (100% in 10563731072) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1532253-4
[M83513/10-D01NP](#) = [MCKS-N1-P-25PRT1](#)

Customers Also Bought



TE Part #216368-001
[22759/33-26-9](#)



TE Part #216550-2
[8/8 PCB MOD.JACK TE](#)



TE Part #1-745491-8
[09 HDE MS RCPT,22-26,LEAD FREE](#)



TE Part #1-1337447-0
[BNC Ins BHSkt 50Ohm Nickel Silver Pltd](#)




TE Part #1532203-1
[M83513/02-CN, MCKS-N1-B-21SS](#)



TE Part #1618239-7
[K40P332=RELAY VACUUM SPST LATC](#)



TE Part #2-2176343-1
[CRGCQ 1206 470R 1%](#)



TE Part #2-5174225-5
[AMPLIMITE 050-2B HOR 68P M2.5](#)



TE Part #CAT-076-BNCVTBAY
[BNC Vertical Jack RF Connector, 50 Ohm, Bayonet Coupling Mechanism](#)

Documents

Product Drawings

[M83513/02-DC, MCKS-C2-B-25SS](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1532204-2_B.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1532204-2_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1532204-2_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.