

# Product data sheet

Specifications



Time delay relay, Harmony SE  
Relays, DPDT, 100ms to 100hours,  
7 time scales, on-delay function,  
socket compatible, 5A, 110V AC

TDR782XBXA-110A

⚠ Discontinued

⚠ Discontinued on: Aug 7, 2023

**Product availability: Non-Stock - Not normally stocked in distribution facility**

## Main

Product Range	Legacy
Product or Component Type	Time delay relay
Switch Function	DPDT
Contacts Material	Silver alloy contacts
Time Delay Type	A
Rated Supply Voltage	110 V AC 50...60 Hz

## Complementary

Time Delay Range	100 ms...1 s 1...10 s 0.1...1 min 1...10 min 0.1...1 h 1...10 h 10...100 h
Control Type	Dial front
Voltage Range	0.85...1.15 Un
Nominal Output Current	5 A
Local Signalling	1 LED amber output status 1 LED green input status
Repeat Accuracy	+/- 0.5 % - 5...5 %
Temperature Drift	+/- 0.05 %/°C
Reset Time	50 ms maximum
Power Consumption in VA	2.6 VA 120 V
Electrical Durability	100000 cycles
Mechanical Durability	10000000 cycles
Mounting Support	Socket
Height	2.3 in (59.4 mm)
Width	0.8 in (21 mm)
Depth	1.06 in (27 mm)
Product Weight	1.8 oz (50 g)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Environment

Dielectric Strength	2000 V between input and output
Standards	IEC 61810-1
Product Certifications	CSA cURus
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-4...140 °F (-20...60 °C)
IP Degree of Protection	IP50 IEC 60529 enclosure)

## Ordering and shipping details

Category	US10CP221127
Discount Schedule	0CP2
GTIN	3606480282966
Returnability	No
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.06 in (2.7 cm)
Package 1 Width	0.83 in (2.1 cm)
Package 1 Length	2.71 in (6.88 cm)
Package 1 Weight	1.5 oz (43 g)
Unit Type of Package 2	S01
Number of Units in Package 2	48
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	913.8 oz (25905 g)



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

[Environmental Disclosure](#)

[Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

SCIP Number

1b9c3411-e0e2-4832-adc7-e6e2a8e06cab

California proposition 65

**WARNING:** This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)


## Use Again

### Repack and remanufacture

Circularity Profile

No need of specific recycling operations

WEEE


 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Dimensions Drawings

Approximate Dimensions


---

**NOTE: Terminal size is 0.105 x 0.020  
(2.68 x 0.508)**



**14 TERMINAL SQUARE  
BASE 4PDT (ON DELAY)**

Approximate Dimensions



Connections and Schema

Connections and Wiring Diagrams

---

