



Positions	A	B	Mode Part #
10	17.26	10.16	35-010-0
14	22.34	15.24	35-014-0
16	24.88	17.78	35-016-0
20	29.96	22.86	35-020-0
24	35.04	27.94	35-024-0
26	37.58	30.48	35-026-0
34	47.74	40.64	35-034-0
40	55.36	48.26	35-040-0
50	68.06	60.96	35-050-0
60	80.96	73.66	35-060-0

**NOTE:**

**Materials**

Insulator: PBT 30% Glass Fiber, UL94V-0  
 Contacts: Brass or Phosphor Bronze  
 Contact Plating: 50µ" Nickel (Underplate)  
 1µ" ~ 30µ" Selective Gold (Contact Area)  
 Insulator Color: Black  
 Env. Prot. Material: **RoHS** Compliant

**Electrical**

Current Rating: 1 Amps  
 Contact Resistance: 20 mΩ Max  
 Insulation Resistance: 1000 MΩ Min  
 Dielectric Withstanding: 500 VDC  
 Operating Temp.: -55°C to 105°C

TITLE		SCALE
<b>.100" RIBBON CONNECTOR</b>		<b>NTS</b>
DRAWING NO.	<b>35-0XX</b>	
		UNITS mm
FILE NAME	35-0XX.pdf	SHEET 1/1



**Mode Electronics Part Number 'multi-parts'**