


**CIRCUIT BREAKERS**



**125VAC  
50VDC**



- |                 |     |                 |     |
|-----------------|-----|-----------------|-----|
| <b>47-503-0</b> | 3A  | <b>47-520-0</b> | 20A |
| <b>47-505-0</b> | 5A  | <b>47-530-0</b> | 30A |
| <b>47-515-0</b> | 15A |                 |     |

Use -1 for Display Package

**MAGNETIC SWITCHES**



Magnetic reed switch for security alarms. Has normally open and normally closed switch contacts. Screw terminals. 30VDC@250ma

- |                 |      |
|-----------------|------|
| <b>47-600-0</b> | Bulk |
| <b>47-600-1</b> | Pkg. |


**FOOT SWITCHES**



- Cast alum. base and guard
- 15Amps @250VAC
- 1 N/C and 1 N/O
- Cable gland included

**47-620-0** Bulk

**ROTARY SWITCHES**



.3 A @ 30VDC non-shorting. Knurled shaft with split.

**48-514-0** 4 pole 3 position  
Use -1 for Display Package

**RELAYS**

**AUTOMOTIVE RELAYS**

Coil Resistance: 90 Ω ± 8%  
Rated Current: 40A@12VDC

**50-835H-0** SPST 12VDC

Coil Resistance: 90 Ω ± 8%  
Rated Current: 30A@12VDC

**50-836H-0** SPDT 12VDC  
Use -1 for Display Package

Coil Resistance: 360 Ω ± 8%  
Rated Current: 20A@24VDC

**50-837H-0** SPST 24VDC



Socket Housing for Auto Relays

c/w 5 terminals

**50-920-0** Auto Relay Socket  
Use -1 for Display Package



Socket for 50-06x and 50-09x relays shown below. Comes with relay hold down spring cup.

**50-901-0** DPDT PC Mount  
Use -1 for Display Package

Socket for 50-06x and 50-09x relays shown below.



50-911-0




50-912-0

- |                 |      |             |
|-----------------|------|-------------|
| <b>50-911-0</b> | DPDT | Screw Term. |
| <b>50-912-0</b> | 4PDT | Screw Term. |

Use -1 for Display Package

**DPDT & 4PDT 5 AMP RELAYS**



- |                        |                    |
|------------------------|--------------------|
| Contact Resistance:    | 50mΩ max.          |
| Operate Time:          | 25ms max.          |
| Release Time:          | 25ms max.          |
| Insulation Resistance: | 100MΩ min.         |
| Mechanical Life:       | 10M cycles         |
| Electrical Life:       | 100K cycles        |
| Resistive Load:        | 5A@28VDC or 250VAC |

Part Number	Circuitry	Oper. Volt.	Coil Res.
<b>50-061-0</b>	DPDT	6VDC	40 Ω
<b>50-063-0</b>	DPDT	12VDC	160 Ω
<b>50-064-0</b>	DPDT	24VDC	650 Ω
<b>50-093-0</b>	4PDT	12VDC	160 Ω
<b>50-094-0</b>	4PDT	24VDC	650 Ω

Use -1 for Display Package


**Visit our Web Site at**  
<http://www.mode-elec.com>



Octal Socket for 50-13x and 50-16x shown above.

**50-910-0** Octal Socket  
Use -1 for Display Package

**10 AMP PC RELAYS**




Contact Resistance: 100mΩ max.  
Operate Time: 8ms max.  
Release Time: 5ms max.  
Insulation Resistance: 100MΩ min.  
Mechanical Life: 10M cycles  
Electrical Life: 100K cycles  
Resistive Load: 10A@28VDC or 10A@125VAC  
Inductive Load: 3A@28VDC or 3A@125VAC

Part Number	Circuitry	Oper. Volt.	Coil Res.
<b>50-530-0</b>	SPDT	5VDC	70 Ω
<b>50-533-0</b>	SPDT	12VDC	400 Ω

Use -1 for Display Package

**3 AMP PC RELAYS**




Contact Resistance: 100mΩ max.  
Operate Time: 10ms max.  
Release Time: 5ms max.  
Insulation Resistance: 100MΩ min.  
Mechanical Life: 10M cycles  
Electrical Life: 500K cycles  
Resistive Load: 3A@28VDC or 120VAC

Part Number	Circuitry	Oper. Volt.	Coil Res.
<b>50-331-0</b>	SPDT	6VDC	180 Ω
<b>50-333-0</b>	SPDT	12VDC	700 Ω

Use -1 for Display Package

**1 AMP PC RELAYS (16-PIN DIP)**



Contact Resistance: 50mΩ max.  
Operate Time: 10ms max.  
Release Time: 4ms max.  
Insulation Resistance: 100MΩ min.  
Mechanical Life: 100M cycles  
Electrical Life: 100K cycles  
Resistive Load: 1A@30VDC or .3A@125VAC

Part Number	Circuitry	Oper. Volt.	Coil Res.
<b>50-430-0</b>	2C	5VDC	125 Ω
<b>50-433-0</b>	2C	12VDC	720 Ω

Use -1 for Display Package

**MODE ELECTRONICS LTD.**  
211 - 2999 UNDERHILL AVE.,  
BURNABY, B.C., CANADA, V5A 3C2  
Phone: 604-435-6633  
Fax: 604-435-8890  
Toll Free: 1-800-663-4992  
Web Site: [www.mode-elec.com](http://www.mode-elec.com)

**Visit our Web Site at**  
<http://www.mode-elec.com>