



Specifications:

1. Material: Copper C2680
Thickness - 0.20mm
2. Plating: Nickel all over thickness at 50 μ "
Gold Flash over Nickel - Thickness at 3 μ "
3. Quantity: 5,000 PCS/Reel (for 30-227-0)
4. General Tolerance: ± 0.15 mm
5. Angle Tolerance: $\pm 1.0^\circ$
6. Wire: 26-28 AWG

TITLE MALE D-SUB CRIMP CONTACTS		SCALE
		NTS
DRAWING NO.	30-226	
		UNITS mm
FILE NAME	<i>30-226.pdf</i>	SHEET 1/1



Mode Electronics Part Number 30-226-0