



## Electrical Commercial and Industrial

[Products](#) | [Documentation & Literature](#) | [News & Tradeshows](#) | [Support](#)[United States](#) > [Energy](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Heat Shrink](#) > [Dual Wall \(Adhesive Lined\)](#) > 3M™ Heat Shrink Thin-Wall Flexible Polyolefin Adhesive-Lined Tubing EPS300-1-48"-Red-24 Pcs, 48 in length sticks, 24 pieces/case[Find An Account Rep](#)[Where To Buy \(Find A Distributor\)](#)[Contact Us](#)

# 3M™ Heat Shrink Thin-Wall Flexible Polyolefin Adhesive-Lined Tubing EPS300-1-48"-Red-24 Pcs, 48 in length sticks, 24 pieces/case

3M ID 80611600257 UPC# 00051128597644 Part Number EPS300-1-48"-Red-24 Pcs

[Print](#)

3M™ EPS-300 Heat Shrink Tubing is a dual-wall tubing provides the advantage of an integral, adhesive-lined construction. This flame-retardant tubing with a 3:1 shrink ratio offers insulation for 600V-rated applications. The flexible polyolefin construction features an internal layer of thermoplastic adhesive, which offers moisture-seal protection in automotive and marine applications.

- Dual-wall construction provides abrasion resistance and moisture-seal protection
- Offers the advantage of integral, adhesive-lined construction
- Offers protection for automotive, truck, electronic components, wire splices, wire bundles and harness breakouts
- Expanded I.D. of 1 in
- 4-ft stick
- Made of red flexible polyolefin
- Withstands temperatures of -67 to 230 degrees F (-55 to 110 degrees C)
- Flame-retardant tubing is rated for 600V applications
- UL Listed, ABS, CSA Certified and RoHS 2011/65/EU Compliant
- 24 sticks/case

### Need Help?

**Questions?** We can help  
[Contact Us](#)

### Overview

### Documents

3M™ Heat Shrink Tubing EPS-300 is color-coded for quick and easy identification of the wire. It provides a skintight fit and strain-relief protection for electronic components, wire splices, wire bundles and harness breakouts. This flame-retardant tubing has a heat shrinkable outer wall that is irradiation cross-linked for abrasion resistance and helps to maintain the high flow as well as superior adhesion characteristics. When the tubing cools down, it forms a permanent, water-resistant barrier. It withstands a wide temperature range of -67 to 230 degrees F (-55 to 110 degrees C). UL Listed, CSA Certified and RoHS 2011/65/EU Compliant.

### Specifications

<b>Brand</b>	3M
<b>Color</b>	Red
<b>Family</b>	3M™ Heat Shrink EPS-300
<b>Length</b>	48 Inch
<b>Material</b>	Polyolefin
<b>Size</b>	1.00 Inch
<b>Trademark</b>	3M

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

**3M:** [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2018. All Rights Reserved.

---