

Search This Product Catalogue

By Keyword

Go

Electrical Products

Product Catalogue for Electrical Products

3M[®] Diagnostic and Detection Products

3M[®] Fire Protection Products

3M[®] Safety and Protection Products

Aerosols, Sprays and Coatings

Insulating, Jacketing and Repair

Low Voltage Splicing (0 - 1000V)

Medium Voltage Splicing and Terminating (5 - 46kV)

Moisture Sealing and Corrosion Protection

New Products

Wire Connecting

Wire Management

[Product Catalogue for Electrical Products](#) [Low Voltage Splicing \(0 - 1000V\)](#) [3M[®] Heat Shrink Splices](#) [3M[®] ITCSN Heavy Wall Cable Sleeves for 1kV](#) [3M[®] ITCSN 1100 Heavy Wall Cable Sleeve](#)

3M[®] ITCSN-1100-48 Heat Shrink Heavy-Wall Cable Sleeve for 1kV, 2 -4/0 AWG, Expanded/Recovered I.D. 1.10/0.37 in, 48 in Length, bulk [Printer-friendly format](#)



3M[®] ITCSN heat shrinkable cable sleeves provide reliable performance for electrical splices, connections and terminations, as well as mechanical and environmental protection. This cable sleeve comes in a length of 48 inch.

[\[click to enlarge\]](#)

3M Order Code : 80 - 0080 - 0726 - 4

Bar Code : 0 00 54007 08972 8

Additional Information

3M[®] ITCSN heat shrinkable heavy - wall cable sleeves are cross - linked polyolefin. They are highly split resistant and fast shrinking to provide rapid installation. The cut - to - length sleeves come standard with a factory - applied adhesive/sealant. Order any of several packaging choices or look for the counter merchandiser assortment at a 3M authorized distributor. Rated to 1 kV, UL Listed 486 D

[Full Text . . .](#)

Learn More . . .

[Packaging Data](#)

Email

[MSDS \(United States\)](#)

Email

[ITCSN Heavy Wall Tubing - Data Sheet \(PDF 25.9 K\)](#)

Please Note:

Adobe[®] Acrobat[®] Reader is required to view PDF documents.

Characteristics

Agency Approvals	ABS
Applicable SAE -AMS-DTL-23053 Specifications	23053/15 class 2
China RoHS - Below MCV	Yes
Color	Black
Dielectric Strength	500 Volt
Elongation	475 Percent
EPC Can View	Contract Only
EU RoHS Compliant	Yes
Expanded Inner Diameter Inches	0.8 Inch
Expanded Inner Diameter Millimetres	20.32 Millimetre
Flammability Rating	Non- Flame Retardant
Length	48 Inch
Non-Corrosive	Yes
Operating Temperature Range (Celsius)	-55 Degrees C to +110 Degrees C
Recovered Inner Diameter Inches	0.37 Inch
Recovered Inner Diameter Millimetres	9.4 Millimetre
Shrink Ratio	3:1
Splice Type	Heat Shrink
Tensile Strength	2400 Pound-Force Per Square Inch
Tubing Types	Heavy Wall