

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0351500200](#)  
**Status:** **Active**  
**Overview:** [VersaBlade Wire-to-Wire Connector System](#)  
**Description:** [VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 2 Circuits, Natural](#)

**Documents:**

<a href="#">3D Model (PDF)</a>	<a href="#">Packaging Specification PK-35150-002-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Brochure (PDF)</a>
<a href="#">Product Specification PS-35150-003-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">35150</a>
Application	Power, Wire-to-Wire
Brochure Order No	987651-4231
Datasheet Order No	987651-3631
Overview	<a href="#">VersaBlade Wire-to-Wire Connector System</a>
Product Name	VersaBlade
UPC	800754375375

**Physical**

Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	1.953/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.20mm
Pitch - Termination Interface	6.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-35150-002-001
Product Specification	PS-35150-003-001
Sales Drawing	SD-35150-020X



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/71/2019 (16 July  
2019)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[35150](#) Series

**Mates With**

VersaBlade Plug Housing [35151](#)

**Use With**

VersaBlade Crimp Terminals [35745](#)  
<br>VersaBlade TPA [351500290](#) ,  
[351500292](#) , [351500293](#) , [351500294](#)