

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0559174030

Status:

Active

Overview:

Description:

2.00mm Pitch MicroClasp Wire-to-Board Header, Dual Row, Vertical, 40 Circuits, without PCB Locator

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	55917
Application	Signal, Wire-to-Board
Overview	microclasp
Product Name	MicroClasp
UPC	756054339060
Physical	
Breakaway	No
Circuits (Loaded)	40
Circuits (maximum)	40
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	2700.500/mg
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.20mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC

Material Info	
Reference - Drawing Numbers	
Application Specification	561340000-AS-000
Packaging Specification	559179200-SPK-200
Product Specification	PS-51353-003-001
Sales Drawing	SD-55917-005

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

55917 Series

Mates With

51353 MicroClasp Wire-to-Board Receptacle Housing

This document was generated on 03/22/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION