

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0783492004](#)
Status: **Active**
Overview: Impact Backplane Connector and Cable Assembly System
Description: Impact 4 Pair, Right-Angle Power Header, Right Hold-Down, Module 1: Blade P1 & P2 Length 5.70mm & 6.90mm; Press-Fit, LCP, Glass Filled UL94-V0, Black, Tray Packaging, Lead-Free

Documents:

[3D Model](#) [Packaging Specification PK-78349-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-78213-001-001 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Backplane Connectors
 Series [78349](#)
 Application Conventional, Coplanar
 Application Tooling Documents TM-622018799
 Component Type Power Header
 Overview [Impact Backplane Connector and Cable Assembly System](#)
 Product Name Impact
 UPC 883906571139

Physical

Circuits (Loaded) 4
 Circuits (maximum) 4
 Color - Resin Black
 Durability (mating cycles max) 200
 First Mate / Last Break Yes
 Flammability 94V-0
 Guide to Mating Part No
 Keying to Mating Part None
 Material - Metal Copper Alloy
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 11.610/g
 Number of Columns N/A
 Number of Pairs 4
 Number of Rows 2
 Orientation Right Angle
 PC Tail Length 2.50mm
 PCB Locator No
 PCB Retention None
 PCB Thickness - Recommended 1.60mm
 Packaging Type Tray
 Pitch - Mating Interface 5.20mm
 Pitch - Termination Interface 2.00mm, 3.20mm
 Plating min - Mating 0.762µm
 Plating min - Termination 2.540µm
 Polarized to PCB No
 Stackable No
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating -55° to +85°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[78349](#) Series

Mates With

[78214](#) Impact Vertical Receptacle, [78350](#) Right Angle Receptacle

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Right-Angle Power Module Installation Press-In Tool	622018642
Impact Power Module Right-Angle Removal Tool	622024500

Termination Interface: Style Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact	20.0A
Data Rate	N/A
Shield Type	N/A
Shielded	No
Voltage - Maximum	250V

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-78349-001-001
Product Specification	PS-78213-001-001
Sales Drawing	SD-78349-001-001
Symbol/Footprint Data	SYM-78349-2004

This document was generated on 09/13/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION