

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [76866-0013](#)
Status: **Active**
Overview: iPass+™ HD Interconnect System
Description: iPass+™ HD Cage and Receptacle 1x4 , 0.76µm, Lead-Free

Documents:
[3D Model](#) [Application Specification AS-76866-002 \(PDF\)](#)
[Drawing \(PDF\)](#) [Test Summary TS-76866-001 \(PDF\)](#)
[Product Specification PS-76866-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-76866-001 \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E107635

General

Product Family	I/O Connectors
Series	76866
Application	Wire-to-Board
Component Type	External Integrated Cage, Receptacle
Electrical Model	Yes
Overview	iPass+™ HD Interconnect System
Product Name	iPass+™
Type	N/A
UPC	884982008250

Physical

Circuits (Loaded)	144
Circuits (maximum)	144
Color - Resin	Black
Durability (mating cycles max)	250
Flammability	94V-0
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	28.888/g
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.37mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.75mm
Pitch - Termination Interface	0.75mm
Plating min - Mating	0.762µm, 1.524µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40°C to +80°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact	1A
Voltage - Maximum	30V AC (RMS)/DC

Material Info




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No**
**Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[76866Series](#)

Mates With
[111068](#) iPass™ Cable Assembly

Application Tooling | FAQ
*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global	
Description	Product #
Press-In Tool	0622030050
HD Removal Tool	0622030060

Reference - Drawing Numbers

Application Specification	AS-76866-001, AS-76866-002
Electrical Model Document	EE-76866-001
Product Specification	PS-76866-001
Sales Drawing	SD-76866-003
Test Summary	TS-76866-001

This document was generated on 12/22/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION