

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015311041](#)
Status: **Active**
Description: 4.80mm Pitch Wire-to-Wire Plug Housing, 4 Circuits

Documents:

| | |
|---|--|
| 3D Model | Product Specification PS-5025-003 (PDF) |
| Drawing (PDF) | Packaging Specification SPK-5025-001 (PDF) |
| Product Specification PS-5025-001 (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-5025-002 (PDF) | |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|----------------|----------------------|
| Product Family | Crimp Housings |
| Series | 5025 |
| Application | Power, Wire-to-Wire |
| Product Name | N/A |
| UPC | 800753604568 |

Physical

| | |
|-------------------------------|-----------------|
| Circuits (maximum) | 4 |
| Flammability | 94V-2 |
| Gender | Plug |
| Glow-Wire Compliant | No |
| Net Weight | 1826.300/mg |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | Yes |
| Pitch - Mating Interface | 4.80mm |
| Pitch - Termination Interface | 4.80mm |
| Polarized to Mating Part | Yes |
| Ports | 1 |
| Stackable | No |
| Temperature Range - Operating | -40°C to +105°C |

Material Info

| | |
|--------------------|----------|
| Engineering Number | 5025-04P |
|--------------------|----------|

Reference - Drawing Numbers

| | |
|-------------------------|---------------------------------------|
| Packaging Specification | SPK-5025-001 |
| Product Specification | PS-5025-001, PS-5025-002, PS-5025-003 |
| Sales Drawing | SD-5025-04P* |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

| | |
|-----------------|---------------|
| China ROHS | Green Image |
| ELV | Not Relevant |
| RoHS Phthalates | Not Contained |

Search Parts in this Series

[5025](#) Series

Mates With

[5025](#) Receptacle

Use With

[5006](#)