

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0932870001](#)
Status: **Active**
Overview: SRC - Sealed Rectangular Connectors
Description: SRC Housing, Female, 84 Pin Signal (84 x MX150™), SPS/Nylon, Black

Documents:

Drawing (PDF)	Packaging Specification 937320001-K (PDF)
Product Specification 850700010-K (PDF)	Test Summary STR-1389-001 (PDF)
Product Specification 937320001-P (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 850830010-A (PDF)	Product Literature (PDF)

General

Product Family	Crimp Housings
Series	93287
Application	Signal, Wire-to-Wire
More Detailed Tech Information	Current (max.) for 84 way fully loaded 6A with 30° temp rise (AWG 14 MX150)
Overview	SRC - Sealed Rectangular Connectors
Product Literature Order No	987650-7391
Product Name	SRC
UPC	884982405226


Physical

Circuits (maximum)	84
Circuits Detail	84 x MX150™
Color - Resin	Black
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	121.830/g
Number of Rows	14
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Material Info

Reference - Drawing Numbers

Application Specification	850830010-A
Packaging Specification	937320001-K
Product Specification	850700010-K, 937320001-P
Sales Drawing	932870001-000
Test Summary	STR-1389-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[93287](#) Series

Mates With

SRC Signal Blade Housing [93288-0001](#) , [93792-8400](#)

Use With

MX150™ Female Terminals [33012](#)