
This document was generated on 05/22/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0194350811
Status: Active
Overview: MX150L™ Industrial Sealed Connector System
Description: MX150L™ 8 Circuit Rear Mounted Flange Plugs for 14-16 AWG Wire, with Gasket



Series image - Reference only

Documents:

- 3D Model
- Drawing (PDF)
- Product Specification PS-19417-001-001 (PDF)
- Packaging Specification PK-19435-001 (PDF)
- RoHS Certificate of Compliance (PDF)
- Product Literature (PDF)

General

Product Family	Crimp Housings
Series	19435
Application	Power, Wire-to-Wire
Comments	Mat Seal Color is Blue. IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Overview	MX150L™ Industrial Sealed Connector System
Product Literature Order No	987650-2181
Product Name	MX150L™
UPC	822350301046

Physical

Circuits (maximum)	8
Gender	Plug
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Net Weight	23.990/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	18.0A

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-19435-001
Product Specification	PS-19417-001-001
Sales Drawing	SD-19435-008

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free Status
Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
19435 Series

Mates With
19418 Receptacle Assemblies

Use With
19417 Male Crimp Terminals

This document was generated on 05/22/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION