

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1511050004](#)
Status: **Active**
Description: 0.50mm Pitch DDR4 miniDIMM Socket, Surface Mount, Vertical, with Natural(Off-White) Latches, without Center Forklock, without Pick and Place Cap, 288 Circuits

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-151105-0001-000 \(PDF\)](#)
[Product Specification PS-151105-0001-001 \(PDF\)](#) [Test Summary TS-151105-0001-001 \(PDF\)](#)
[Application Specification AS-151105-0001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-151105-0002-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Memory Module Sockets
 Series [151105](#)
 Component Type Socket
 JEDEC Outline MO-314
 Product Name DDR4 MiniDIMM
 UPC 889056426541

Physical

Circuits (Loaded) 288
 Circuits (maximum) 288
 Durability (mating cycles max) 25
 Entry Angle Vertical (Top Entry)
 Flammability 94V-0
 Housing Color Black
 Keying to Mating Part None
 Latch Color Natural (Off-White)
 Material - Metal Copper Alloy
 Material - Plating Mating Gold over Nickel
 Material - Plating Termination Tin over Nickel
 Material - Resin Liquid Crystal Polymer
 Net Weight 3.810/g
 PCB Locator Yes
 PCB Retention Yes
 Packaging Type Tray
 Pitch - Mating Interface 0.50mm
 Plating min - Mating 0.762µm
 Plating min - Termination 2.540µm
 Temperature Range - Operating -55° to +85°C
 Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 0.75A
 Voltage - Maximum 29V AC (RMS)/DC
 Voltage Key 1.2V

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
 Lead-free Process Capability REFLOW
 Max. Cycles at Max. Process Temperature 002
 Process Temperature max. C 260

Material Info



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/71/2019 (16 July
 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[151105 Series](#)

Mates With

[JEDEC MO-314 Memory Modules](#)

Reference - Drawing Numbers

Application Specification	AS-151105-0001-001, AS-151105-0002-001
Electrical Model Document	EE-151105-0001
Packaging Specification	PK-151105-0001-000
Product Specification	PS-151105-0001-001
S-Parameter Model	SP-151105-0001
Sales Drawing	SD-151105-0001-000
Signal Integrity Report	SI-151105-0001
Test Summary	TS-151105-0001-001

This document was generated on 09/19/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION