

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0462070024](#)
Status: **Active**
Overview: [Mini-Fit Jr. Power Connectors](#)
Description: 4.20mm Pitch, Mini-Fit Jr.™ Reflow Solder Capable Header, Dual Row, Vertical, 24 Circuits, 1.57mm PCB Thickness, with PCB Pegs, LCP Housing, with Tin (Sn) Over Nickel (Ni) Plating, Glow Wire Capable

Documents:

[3D Model](#) [Packaging Specification PK-46207-001-000 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-46207-001-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family PCB Headers
 Series [46207](#)
 Application Board-to-Board, Power, Wire-to-Board
 Comments Current for wire-to-wire applications = 13.0A max. per circuit. Current for wire-to-board applications = 9.0A max. per circuit
 MolexKits Yes
 Overview [Mini-Fit Jr. Power Connectors](#)
 Product Name Mini-Fit Jr.™
 UPC 800756675800

Physical

Breakaway No
 Circuits (Loaded) 24
 Circuits (maximum) 24
 Color - Resin Black
 Durability (mating cycles max) 100
 First Mate / Last Break No
 Flammability 94V-0
 Glow-Wire Compliant Yes
 Guide to Mating Part No
 Lock to Mating Part Yes
 Material - Metal Brass
 Material - Plating Mating Matte Tin
 Material - Plating Termination Matte Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 8.067/g
 Number of Rows 2
 Orientation Vertical
 PC Tail Length 3.66mm
 PCB Locator Yes
 PCB Retention Yes
 PCB Thickness - Recommended 1.57mm
 Packaging Type Tray
 Pitch - Mating Interface 4.20mm
 Pitch - Termination Interface 4.20mm
 Polarized to Mating Part Yes
 Polarized to PCB Yes
 Shrouded Fully
 Stackable No



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Green Image
 ELV Not Relevant
 RoHS Phthalates Not Contained

Search Parts in this Series

[46207 Series](#)

Mates With

[5557 Mini Fit Jr.™ Receptacle](#)

Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V AC (RMS)/DC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	030
Lead-free Process Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	265
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-46207-001-000
Product Specification	PS-46207-001-001
Sales Drawing	SD-46207-001-000

This document was generated on 08/18/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION